

Copper Building Wire
 Base Price: PG CQH - 259
 Base Price Effective Date: 4/15/2024

*This sheet replaces Price List PG CQH - 258 dated 4/04/2024



SOLID CONDUCTORS										
AWG Size	THHN	XHHW-2	USE-2	Packaging			Cuts	Parallels		
				Cartons	Std Reels	LL Reels		2 Legs	3 Legs	4 Legs
14	\$ 126.93	***	***	4 x 500 ft	2,500 ft	No	***	***	***	***
12	\$ 194.73	***	***	4 x 500 ft	2,500 ft	No	***	***	***	***
10	\$ 304.67	***	***	2 x 500 ft	2,500 ft	No	***	***	***	***

STRANDED CONDUCTORS										
AWG Size	THHN / TFFN	XHHW-2	USE-2	Packaging			Cuts	Parallels		
				Cartons	Std Reels	LL Reels		2 Legs	3 Legs	4 Legs
18	\$ 76.88	***	***	4 x 500 ft	2,500 ft	No	***	***	***	***
16	\$ 107.33	***	***	4 x 500 ft	2,500 ft	No	***	***	***	***
14	\$ 141.18	\$ 190.11	***	4 x 500 ft	2,500 ft	No	***	***	***	***
12	\$ 208.63	\$ 258.08	***	4 x 500 ft	2,500 ft	No	***	***	***	***
10	\$ 319.07	\$ 386.70	***	2 x 500 ft	2,500 ft	No	***	***	***	***
8	\$ 592.26	\$ 686.78	\$ 818.35	n/a	500 ft / 1,000 ft	Yes	\$ 40.00	\$ 80.00	\$ 120.00	\$ 160.00
6	\$ 911.21	\$ 1,043.21	\$ 1,180.94	n/a	500 ft / 1,000 ft	Yes	\$ 40.00	\$ 80.00	\$ 120.00	\$ 160.00
4	\$ 1,394.41	\$ 1,535.11	\$ 1,799.36	n/a	5,000 ft	Yes	\$ 40.00	\$ 80.00	\$ 120.00	\$ 160.00
3	\$ 1,758.79	\$ 1,886.89	***	n/a	5,000 ft	Yes	\$ 40.00	\$ 80.00	\$ 120.00	\$ 160.00
2	\$ 2,201.46	\$ 2,369.01	\$ 2,795.70	n/a	5,000 ft	Yes	\$ 40.00	\$ 80.00	\$ 120.00	\$ 160.00
1	\$ 2,453.09	\$ 2,598.59	\$ 2,998.27	n/a	5,000 ft	Yes	\$ 40.00	\$ 80.00	\$ 120.00	\$ 160.00
1/0	\$ 3,003.40	\$ 3,194.08	\$ 3,824.33	n/a	5,000 ft	Yes	\$ 40.00	\$ 80.00	\$ 120.00	\$ 160.00
2/0	\$ 3,699.62	\$ 3,991.73	\$ 4,807.26	n/a	5,000 ft	Yes	\$ 40.00	\$ 80.00	\$ 120.00	\$ 160.00
3/0	\$ 4,669.05	\$ 4,997.20	\$ 6,007.26	n/a	5,000 ft	Yes	\$ 40.00	\$ 80.00	\$ 120.00	\$ 160.00
4/0	\$ 5,828.21	\$ 6,267.46	\$ 7,502.64	n/a	5,000 ft	Yes	\$ 40.00	\$ 80.00	\$ 120.00	\$ 160.00
250	\$ 6,753.46	\$ 7,228.22	\$ 8,061.00	n/a	5,000 ft	Yes	\$ 40.00	\$ 80.00	\$ 120.00	\$ 160.00
300	\$ 8,099.07	\$ 8,593.60	\$ 9,209.03	n/a	6,000 ft	Yes	\$ 40.00	\$ 80.00	\$ 120.00	\$ 160.00
350	\$ 9,483.22	\$ 10,040.49	\$ 10,940.98	n/a	2,500 ft	Yes	\$ 40.00	\$ 80.00	\$ 120.00	\$ 160.00
400	\$ 10,787.66	\$ 11,449.39	\$ 12,406.08	n/a	5,000 ft	Yes	\$ 40.00	\$ 80.00	\$ 120.00	\$ 160.00
500	\$ 13,631.02	\$ 14,280.54	\$ 15,032.11	n/a	2,500 ft	Yes	\$ 40.00	\$ 80.00	\$ 120.00	\$ 160.00
600	\$ 16,985.54	\$ 18,033.05	\$ 18,719.43	n/a	2,000 ft	Yes	\$ 40.00	\$ 80.00	\$ 120.00	\$ 160.00
750	\$ 28,712.09	\$ 29,386.52	\$ 30,512.90	n/a	3,000 ft	Yes	\$ 40.00	\$ 80.00	\$ 120.00	\$ 160.00

Orders are subject to all other Prysmian Terms & Conditions

Copper Building Wire Terms & Conditions

Base Price Effective Date: 4/15/2024

PRICING:

PRICING SHOWN IS PER 1,000 FEET
PRICING IS FIRM FOR IMMEDIATE RELEASE AND SHIP
PRICING IS SUBJECT TO CHANGE WITHOUT NOTICE

QUOTE VALIDITY:

PRYSMIAN COPPER BUILDING WIRE QUOTES ARE VALID FOR 24 HOURS UNLESS OTHERWISE NOTED

MINIMUM ORDER VALUE: \$1,000.00

PAYMENT TERMS:

NET 30 DAYS - UNLESS OTHERWISE AGREED TO BY BOTH PARTIES PRIOR TO ORDER ACCEPTANCE

FREIGHT CHARGES:

FREIGHT IS PRE-PAID & ALLOWED ON ORDERS OF 5,000 POUNDS. CIP ORIGIN WITHIN THE CONTIGUOUS UNITED STATES.
BUYER SHALL BE RESPONSIBLE FOR MATERIAL IDENTIFICATION, COUNT, AND VISUAL INSPECTION FOR DAMAGE UPON RECEIPT OF SHIPMENT WITHIN 48 HOURS OF DELIVERY. RETURNS FOR CUT OR TERMINATED WIRE WILL NOT BE ACCEPTED.

CUT CHARGES: \$40 PER CUT

CUT CHARGES APPLY TO ALL NON-STANDARD LENGTHS.
NO CHARGE ON LENGTHS 500', 1000', 2000', 2500' AND 5000'.
NO CUTS UNDER 100 FEET

CUTTING TOLERANCE:

FOR ANY CUT PERFORMED BY PRYSMIAN , -10% / +10% CUTTING TOLERANCE APPLIES.

PARALLEL CHARGES: \$40 PER LEG PER REEL

*NOTE: PARALLELING CHARGES INCLUDE THE CUT CHARGES.
PARALLELING CHARGES APPLY PER REEL, PER LENGTH
NO PARALLELS UNDER 100 FEET

PULLING EYES: \$50 EACH

CRADLING: \$60 EACH

WOOD LAGGING: \$400 PER REEL

LEAD TIMES:

ALL STOCK AVAILABILITY IS SUBJECT TO PRIOR SALE.
LEAD TIMES ARE BASED ON CURRENT FACTORY CAPACITY AND ARE SUBJECT TO CHANGE WITHOUT NOTICE.
PLEASE CONSULT YOUR INSIDE SALES REPRESENTATIVE FOR AVAILABLE STOCK AND CURRENT LEAD TIMES

WILL CALL ORDERS (SOUTHERN CALIFORNIA ONLY):

PRYSMIAN ORDER NUMBER REQUIRED WHEN PICKING UP ORDERS.
ORDERS MUST BE PICKED UP WITHIN 24 HOURS OR ORDER IS SUBJECT TO SHIPMENT AT CUSTOMER'S EXPENSE
NO BACKORDERS WILL BE ALLOWED FOR WILL CALL ORDERS

MAKE TO ORDER / NON-STOCK PRODUCTS:

CUSTOMER TO TAKE ALL LENGTHS GENERATED

BUILDING WIRE ORDERS:

ALL BUILDING WIRE ORDERS ARE NON-CANCELABLE AND NON-RETURNABLE.
25% RESTOCKING FEE WILL APPLY TO ANY EXCEPTIONS TO THIS RULE

TEST RESULT DATA REPORTS:

COC: NO CHARGE
CER: \$25.00 PER ITEM ORDERED
CTR / CTD: \$250.00 PER ITEM ORDERED
TEST REPORTS MUST BE REQUESTED AT THE TIME OF ORDER PLACEMENT

ORDER ACCEPTANCE:

ORDERS ARE BINDING ONLY AFTER ACCEPTANCE BY PRYSMIAN.
ALL TRANSACTIONS ARE SUBJECT TO PRYSMIAN STANDARD TERMS & CONDITIONS, UNLESS OTHERWISE NOTED PRIOR TO THE SALE