

Outdoor Extension Cords



Prysmian, under the CAROL® Brand name, offers a complete line of high-quality Outdoor Extension Cords designed to provide the best electrical performance for your application.

CAROL® FrogHide® Ultra Flex® extension cords are the most flexible, durable rubber outdoor cords on the market with a name you won't forget, and they now feature a connector end that lights up to indicate the power is on. FrogHide cords are bonded to the caps and connectors, with heavy-duty strain reliefs built in for lasting strength, even in rough applications. Plus, they are resistant to water, oil, ozone and chemicals. FrogHide cords feature an exclusive personal identification system, so you can claim them as your own. They are easy to spot on the job, thanks to the bold, bright green color. FrogHide extension cords come with a limited lifetime warranty.

Lifetime Plus® Super Flex® extension cords have a connector end that lights up to indicate the power is on. Twice as flexible as other extension cords, the high-visibility yellow cord resists moisture and will not crack in arctic cold or melt in desert heat. The super-tough jacket provides extra resistance to cracking and abrasion. Lifetime Plus extension cords remain flexible to -50° C.

The CAROL® line of All Weather extension cords and High Visibility All Weather extension cords are designed for excellent performance, even in freezing temperatures. These blue outdoor cords remain flexible to -50° C.

Safety Orange® general-purpose outdoor extension cords and Powr-Centers® are basic necessities for every household tool box. The familiar orange jacket provides excellent visibility for improved safety on the job.

FrogHide® Ultra Flex® Lighted Extension Cords

3-Conductor Grounded • Type SJOW • -40°C to 90°C • 300 Volts



CATALOG NUMBER	NO. OF COND.	AWG SIZE	LENGTH OF CORD (FT)	COLOR OF JACKET	POWER RATING			PKG. PER CTN.	WT./ UNIT LBS	WT./ CTN. LBS	UPC CODE
					VOLTS	AMPS	WATTS				
06425.63.06L	3	14	25	Green	125	15	1875	10	3.0	30	079407064250
06450.63.06L	3	14	50	Green	125	15	1875	6	6.0	36	079407064502
06400.63.06L	3	14	100	Green	125	13	1625	4	11.4	46	079407064007
06225.61.06L	3	12	25	Green	125	15	1875	6	4.3	26	079407062256
06250.61.06L	3	12	50	Green	125	15	1875	4	7.9	32	079407062508
06200.61.06L	3	12	100	Green	125	15	1875	2	15.9	32	079407062003



Product Description:

Carol® Brand FrogHide® Ultra Flex® extension cords are the most flexible, durable rubber outdoor cords on the market with a name you won't forget, and they now feature a connector end that lights up to indicate the power is on. FrogHide cords are bonded to the caps and connectors with heavy-duty strain reliefs built in for lasting strength, even in rough applications. Plus, they are resistant to water, oil, ozone and chemicals. FrogHide cords feature an exclusive personal identification system, so you can claim them as your own. They are easy to spot on the job, thanks to the bold, bright green color. FrogHide extension cords come with a limited lifetime warranty.

Product Warranty:

Carol® Brand FrogHide® Ultra Flex® Limited Lifetime Warranty
 This product is covered by a limited lifetime warranty against manufacturing defects. If you are not satisfied with this cord, return it with the original packaging to Prysmian, 4 Tesseneer Drive, Highland Heights, KY 41076 for evaluation. This warranty does not cover damage to the cord from long-term use, abuse or from failure to follow electrical codes, laws and regulations relating to building or construction, including Article 590 of the National Electrical Code®. This warranty gives you specific legal rights, and you may also have other rights that vary from state to state.

Product Construction:

- Conductor:**
 - 14 AWG or 12 AWG stranded bare copper
- Insulation:**
 - Premium-grade, color-coded 90°C EPDM
- Jacket:**
 - CPE; green
 - Temperature range: -40°C to 90°C
 - Voltage rating: 300 volts
- NEMA Configuration:**
 - 5-15P/5-15R

Applications:

- Chain saws
- Wet/dry vacs
- Orbital sanders
- Other outdoor equipment

Features:

- Connector lights up with power
- New technology bonds cap and connector
- Ultra-flexible
- Heavy-duty strain relief
- Personal identification system
- Resistant to water, oil, ozone and chemicals
- Limited lifetime warranty
- 3-conductor grounded

Industry Approvals:

- UL Listed
- OSHA Acceptable



Lifetime Plus® Super Flex® Lighted Extension Cords

3-Conductor Grounded · Type SJTW · -50°C to 60°C · 300 Volts



CATALOG NUMBER	NO. OF COND.	AWG SIZE	LENGTH OF CORD (FT)	COLOR OF JACKET	TYPE	POWER RATING			PKG. PER CTN.	WT./UNIT LBS	WT./CTN. LBS	UPC CODE
						VOLTS	AMPS	WATTS				
1 GROUNDED OUTLET												
03387.63.05	3	16	25	Yellow	SJTW	125	13	1625	12	1.7	20	079407033874
03390.63.05	3	14	25	Yellow	SJTW	125	15	1875	12	2.5	30	079407033904
03391.63.05	3	14	50	Yellow	SJTW	125	15	1875	6	4.7	28	079407033911
03392.63.05	3	14	100	Yellow	SJTW	125	13	1625	4	9.2	37	079407033928
03397.61.05	3	12	25	Yellow	SJTW	125	15	1875	6	3.7	22	079407033973
03398.61.05	3	12	50	Yellow	SJTW	125	15	1875	4	7.0	28	079407033980
03399.61.05	3	12	100	Yellow	SJTW	125	15	1875	2	13.1	26	079407033997
3 GROUNDED OUTLETS												
03350.63.05	3	12	2	Yellow	SJTW	125	15	1875	6	1.0	6	079407033508
03351.61.05	3	12	25	Yellow	SJTW	125	15	1875	6	4.2	25	079407416592
03352.61.05	3	12	50	Yellow	SJTW	125	15	1875	4	7.5	30	079407416608
03353.61.05	3	12	100	Yellow	SJTW	125	15	1875	2	13.6	27	079407416615

Product Description:

Lifetime Plus® Super Flex® extension cords have a connector end that lights up to indicate the power is on. Twice as flexible as other extension cords, the high-visibility yellow cord resists moisture and will not crack in arctic cold or melt in desert heat. The super-tough jacket provides extra resistance to cracking and abrasion. The Lifetime Plus extension cords have a limited lifetime warranty and remain flexible to -40°C.

Product Construction:

Conductor:

- 16 AWG, 14 AWG or 12 AWG stranded bare copper per ASTM B174

Insulation:

- Premium-grade, color-coded PVC

Jacket:

- PVC; yellow
- Temperature range: -40°C to 60°C
- Voltage rating: 300 volts

NEMA Configuration:

- 5-15P/5-15R

Applications:

- Chain saws
- Wet/dry vacs
- Orbital sanders
- Other outdoor equipment

Features:

- Lights up with power
- Super-flexible
- Weather- and water-resistant
- Limited lifetime warranty
- 3-conductor grounded
- 1 grounded outlet: 16 AWG-12 AWG
- 3 grounded outlets: 12 AWG only

Industry Approvals:

- UL Listed
- OSHA Acceptable

Safety Orange® Extension Cords

3-Conductor Grounded • Type SJTW • -40°C to 60°C • 300 Volts

CATALOG NUMBER	NO. OF COND.	AWG SIZE	LENGTH OF CORD (FT)	COLOR OF JACKET	POWER RATING			PKG. PER CTN.	WT./UNIT LBS	WT./CTN. LBS	UPC CODE
					VOLTS	AMPS	WATTS				
03318.63.04	3	16	10	Orange	125	13	1625	24	0.8	19	079407033188
03327.63.04	3	16	25	Orange	125	13	1625	24	1.8	43	079407033270
03354.63.04	3	16	50	Orange	125	13	1625	12	3.4	40	079407033546
03302.63.04	3	16	100	Orange	125	10	1250	4	6.6	26	079407033027
03328.63.04	3	14	25	Orange	125	15	1875	6	2.4	14	079407033287
03356.63.04	3	14	50	Orange	125	15	1875	4	4.6	18	079407033560
03304.63.04	3	14	100	Orange	125	13	1625	2	9.0	18	079407033041
06826.63.04	3	12	25	Orange	125	15	1875	4	3.4	14	079407068265
06853.63.04	3	12	50	Orange	125	15	1875	2	6.6	13	079407068531
06801.63.04	3	12	100	Orange	125	15	1875	2	13.0	26	079407068012



Product Construction:

Conductor:

- 16 AWG through 12 AWG stranded bare copper per ASTM B174

Insulation:

- Premium-grade, color-coded PVC

Jacket:

- PVC; orange
- Temperature range: -40°C to 60°C
- Voltage rating: 300 volts

NEMA Configuration:

- 5-15P/5-15R

Applications:

- General use indoor/outdoor cord
- Vacuum cleaners
- Floor polishers
- Sanders
- Other power equipment

Features:

- Indoor/outdoor use
- 3-conductor grounded

Industry Approvals:

- UL Listed
- OSHA Acceptable

Outdoor Powr-Center® Extension Cords

3-Conductor Grounded • Types STW, SJEOOW and SJTW • -40°C to 60 °C
• 300 and 600 Volts



CATALOG NUMBER	NO. OF COND.	AWG SIZE	LENGTH OF CORD (FT)	COLOR OF JACKET	POWER RATING			PKG. PER CTN.	WT./UNIT LBS	WT./CTN. LBS	UPC CODE
					VOLTS	AMPS	WATTS				

STW-600 V

00594.63.04	3	12	2	Orange	125	15	1875	6	1.0	6	079407005949
00596.61.04	3	12	50	Orange	125	15	1875	2	11.1	22	079407005963
00597.61.04	3	12	100	Orange	125	15	1875	2	21.7	43	079407005970

SJTW-300 V

00690.63.04	3	14	10	Orange	125	15	1875	12	1.2	15	079407006908
00691.63.04	3	14	25	Orange	125	15	1875	6	2.6	16	079407006915
00692.63.04	3	14	50	Orange	125	15	1875	4	4.7	19	079407006922
00694.63.04	3	12	10	Orange	125	15	1875	12	1.8	22	079407006946
00696.63.04	3	12	50	Orange	125	15	1875	2	7.0	14	079407006960
00697.63.04	3	12	100	Orange	125	15	1875	2	13.4	27	079407006977

ALL WEATHER HIGH VISIBILITY SJEOOW-300 V

00790.63.07	3	14	10	Blue	125	15	1875	12	1.3	16	079407007905
00791.63.07	3	14	25	Blue	125	15	1875	6	2.7	16	079407007912
00792.63.07	3	14	50	Blue	125	15	1875	4	4.8	19	079407007929
00793.63.07	3	14	100	Blue	125	13	1625	2	9.0	18	079407007936
00787.63.05	3	12	50	Yellow	125	15	1875	2	6.5	13	079407007875
00788.63.05	3	12	100	Yellow	125	15	1875	2	13.0	26	079407007882

Product Construction:

Conductor:

- 14 AWG or 12 AWG stranded bare copper per ASTM B174

Insulation:

- Premium-grade, color-coded PVC

Jacket:

- PVC; orange, TPE; blue or yellow
- Temperature range: -40 °C to 60 °C
- Voltage rating: 300 and 600 volts

NEMA Configuration:

- 5-15P/5-15R

Applications:

- General use indoor/outdoor cord
- Chain saws
- Wet/dry vacs
- Orbital sanders
- Other power equipment

Features:

- Indoor/outdoor use
- 3 grounded outlets

Industry Approvals:

- UL Listed
- OSHA Acceptable

All Weather Extension Cords

3-Conductor Grounded • Type SJEOOW • -50 °C to 105 °C • 300 Volts

CATALOG NUMBER	NO. OF COND.	AWG SIZE	LENGTH OF CORD (FT)	COLOR OF JACKET	POWER RATING			PKG. PER CTN.	WT./ UNIT LBS	WT./ CTN. LBS	UPC CODE
					VOLTS	AMPS	WATTS				
03654.63.07	3	16	25	Blue	125	13	1625	4	1.8	7	079407036547
03655.63.07	3	16	50	Blue	125	13	1625	4	3.2	13	079407036554
03660.63.07	3	14	25	Blue	125	15	1875	4	2.2	9	079407036608
03661.63.07	3	14	50	Blue	125	15	1875	4	4.3	17	079407036615
03662.63.07	3	14	100	Blue	125	13	1625	2	8.0	16	079407036622
03667.63.07	3	12	50	Blue	125	15	1875	2	6.5	13	079407036677
03668.63.07	3	12	100	Blue	125	15	1875	2	12.5	25	079407036684



Product Description:

The Carol® line of All Weather Extension Cords are designed for excellent performance, even in freezing temperatures. The blue outdoor cords remain flexible and resist cracking to -50 °C.

Product Construction:

Conductor:

- 16 AWG through 12 AWG stranded bare copper per ASTM B174

Insulation:

- Premium-grade, color-coded PVC

Jacket:

- TPE; blue
- Temperature range: -50 °C to 105 °C
- Voltage rating: 300 volts

NEMA Configuration:

- 5-15P/5-15R

Applications:

- Snow blowers
- Engine heaters
- Battery chargers
- Other outdoor equipment

Features:

- Flexible from -50 °C to 105 °C
- For harsh weather conditions
- 3-conductor grounded

Industry Approvals:

- UL Listed
- OSHA Acceptable

High Visibility All Weather Extension Cords

3-Conductor Grounded • Type SJEOOW • -50 °C to 105 °C • 300 Volts

CATALOG NUMBER	NO. OF COND.	AWG SIZE	LENGTH OF CORD (FT)	COLOR OF JACKET	POWER RATING			PKG. PER CTN.	WT./ UNIT LBS	WT./ CTN. LBS	UPC CODE
					VOLTS	AMPS	WATTS				
03685.61.05	3	10	50	Yellow	125	15	1875	2	12.5	25	079407036851
03686.61.05	3	10	100	Yellow	125	15	1875	2	24.5	49	079407036868



Product Construction:

Conductor:

- 10 AWG stranded bare copper per ASTM B174

Insulation:

- Premium-grade, color-coded premium PVC

Jacket:

- TPE; yellow
- Temperature range: -50 °C to 105 °C
- Voltage rating: 300 volts

NEMA Configuration:

- 5-15P/5-15R

Applications:

- Heavy construction equipment
- Air compressors
- Circular saws
- Generators

Industry Approvals:

- UL Listed
- OSHA Acceptable



OSHA Acceptable
Occupational Safety and Health
Administration

