

Application-Specific Extension Cords



Prysmian offers a complete line of Power Supply Replacement Cords for use with power tools and household appliances. The three-conductor cords have either right angle or straight caps with a variety of plug configurations. The free ends are conveniently slit for ease of connection.

CAROL[®] Brand Range Cords and Dryer Cords are available in three-wire and four-wire constructions, with an assortment of plug configurations. They are designed to accommodate virtually any household oven/range or clothes dryer.

CAROL[®] offers a wide assortment of Major Appliance Extension Cords with a variety of plug and cap configurations for use with air conditioners, refrigerators, freezers, microwave ovens, dehumidifiers and other large household appliances.

Pro Flex® Rubber Extension Cords

3-Conductor Grounded • Type SJ • 60°C • 300 Volts

| CATALOG NUMBER | NO. OF COND. | AWG SIZE | LENGTH OF CORD (FT) | COLOR OF JACKET | POWER RATING | | | NEMA CONFIG. | PKG. PER CTN. | WT./ UNIT LBS | WT./ CTN. LBS | UPC CODE |
|----------------|--------------|----------|---------------------|-----------------|--------------|------|-------|--------------|---------------|---------------|---------------|--------------|
| | | | | | VOLTS | AMPS | WATTS | | | | | |
| 06610.63.01 | 3 | 16 | 10 | Black | 125 | 13 | 1625 | 5-15P/5-15R | 24 | 0.7 | 17 | 079407066100 |
| 06625.63.01 | 3 | 16 | 25 | Black | 125 | 13 | 1625 | 5-15P/5-15R | 24 | 1.7 | 40 | 079407066254 |
| 06911.63.01 | 3 | 14 | 25 | Black | 125 | 15 | 1875 | 5-15P/5-15R | 12 | 2.3 | 14 | 079407069118 |



Product Construction:

Conductor:

- 16 AWG through 14 AWG stranded bare copper per ASTM B174

Insulation:

- Premium-grade, color-coded EPDM

Jacket:

- CPE; black
- Temperature: 60°C
- Voltage rating: 300 volts

Applications:

- Floor polishers
- Sanders

Features:

- General use indoor cord
- 3-conductor grounded

Industry Approvals:

- UL Listed
- OSHA Acceptable for indoor use

Coiled Power Tool Extension Cords and Power Supply Cords

2 and 3 Conductor • Type SJT • 60°C • 300 Volts

| CATALOG NUMBER | NO. OF COND. | AWG SIZE | LENGTH OF CORD (FT) | COLOR OF JACKET | POWER RATING | | | NEMA CONFIG. | PKG. PER CTN. | WT./ UNIT LBS | WT./ CTN. LBS | UPC CODE |
|----------------|--------------|----------|---------------------|-----------------|--------------|------|-------|--------------|---------------|---------------|---------------|--------------|
| | | | | | VOLTS | AMPS | WATTS | | | | | |
| 06014.60.04 | 3 | 16 | 10 | Orange | 125 | 13 | 1625 | 5-15P/5-15R | 10 | 1.1 | 11 | 079407060146 |
| 02551.70.01 | 3 | 16 | 12 | Black | 125 | 15 | 1875 | 5-15P | 10 | 1.1 | 11 | 079407025510 |



Product Construction:

Conductor:

- 16 AWG stranded bare copper per ASTM B174

Insulation:

- Premium-grade, color-coded PVC

Jacket:

- PVC; orange or black
- Voltage rating: 300 volts

Applications:

- Workshop and tool bench use

Features:

- Coiled cord expands from 3' to 10' or 12'
- Right-angle plug helps prevent the cord from being pulled from the socket

Features (cont'd.):

- 06014.60.04 and 02551.70.01 are 3-conductor grounded

Industry Approvals:

- UL Listed
- OSHA Acceptable

Power Supply Replacement Cords with Switch

3-Conductor Grounded • Type SJT • 60°C • 300 Volts

| CATALOG NUMBER | NO. OF COND. | AWG SIZE | LENGTH OF CORD (FT) | COLOR OF JACKET | POWER RATING | | | NEMA CONFIG. | SWITCH SPEED | PKG. PER CTN. | WT./ UNIT LBS | WT./ CTN. LBS | UPC CODE |
|----------------|--------------|----------|---------------------|-----------------|--------------|------|-------|--------------|------------------|---------------|---------------|---------------|-------------|
| | | | | | VOLTS | AMPS | WATTS | | | | | | |
| 02336.70.01 | 3 | 16 | 10 | Black | 125 | 13 | 1650 | 5-15P | 1 Speed (On/Off) | 25 | 0.9 | 22 | 07940743242 |

Product Construction:

Conductor:

- 16 AWG stranded bare copper per ASTM B174

Insulation:

- Premium-grade, color-coded PVC

Jacket:

- PVC; black

Applications:

- For replacement use
- For fan replacements

Features:

- Switch
- Straight plug
- Conductor stripped 5/8"
- Jacket removed 2"

Industry Approvals:

- UL Listed
- CSA



Power Supply Replacement Cords

3-Conductor Grounded • Types SJ, SJOW and SJOOW • 60° C • 300 Volts



| CATALOG NUMBER | CORD TYPE | NO. OF COND. | AWG SIZE | LENGTH OF CORD (FT) | COLOR OF JACKET | POWER RATING | | | NEMA CONFIG. | PLUG CONFIG. | PKG. PER CTN. | WT./UNIT LBS | WT./CTN. LBS | UPC CODE |
|----------------|-----------|--------------|----------|---------------------|-----------------|--------------|------|-------|--------------|--------------|---------------|--------------|--------------|--------------|
| | | | | | | VOLTS | AMPS | WATTS | | | | | | |
| 02685.70.01 | SJOOW | 3 | 18 | 8 | Black | 125 | 10 | 1250 | 5-15P | Straight | 25 | 0.6 | 14 | 079407026852 |
| 02686.70.01 | SJOW | 3 | 16 | 8 | Black | 125 | 13 | 1625 | 5-15P | Straight | 35 | 0.7 | 24 | 079407026869 |
| 04932.70.01 | SJ | 3 | 16 | 12 | Black | 125 | 13 | 1625 | 5-15P | Straight | 50 | 0.8 | 40 | 079407049325 |
| 04929.70.01 | SJ | 3 | 16 | 9 | Black | 125 | 13 | 1625 | 5-15P | Straight | 50 | 0.6 | 30 | 079407049295 |
| 04926.70.01 | SJ | 3 | 16 | 6 | Black | 125 | 13 | 1625 | 5-15P | Straight | 50 | 0.6 | 28 | 079407049264 |

Product Construction:

Conductor:

- 18 AWG or 16 AWG stranded bare copper per ASTM B174

Insulation:

- Premium-grade, color-coded EPDM

Jacket:

- CPE; black

Applications:

- For replacement use

Features:

- For replacement use
- Straight plug

Industry Approvals:

- UL Listed
- CSA

Power Supply Replacement Cords

2 and 3 Conductor • Types SJT and ST • 60° C • 300 Volts and 600 Volts



| CATALOG NUMBER | CORD TYPE | NO. OF COND. | AWG OF CORD SIZE | LENGTH OF CORD (FT) | COLOR OF JACKET | POWER RATING | | | NEMA CONFIG. | PLUG CONFIG. | PKG. PER CTN. | WT./UNIT LBS | WT./CTN. LBS | UPC CODE |
|-----------------|-----------|--------------|------------------|---------------------|-----------------|--------------|------|-------|--------------|--------------|---------------|--------------|--------------|--------------|
| | | | | | | VOLTS | AMPS | WATTS | | | | | | |
| 300 Volt | | | | | | | | | | | | | | |
| 02523.73.01 | SJT | 3 | 18 | 3 | Black | 125 | 10 | 1250 | 5-15P | Straight | 50 | 0.2 | 12 | 079407025237 |
| 01364.70.01 | SJT | 3 | 18 | 8'2" | Black | 125 | 10 | 1250 | 5-15P | Straight | 50 | 0.5 | 25 | 079407213641 |
| 02524.73.01 | SJT | 3 | 16 | 3 | Black | 125 | 13 | 1625 | 5-15P | Straight | 50 | 0.3 | 14 | 079407025244 |
| 02547.70.01 | SJT | 3 | 16 | 6 | Black | 125 | 13 | 1625 | 5-15P | Straight | 25 | 0.5 | 13 | 079407018444 |
| 01513.70.01 | SJT | 3 | 16 | 8'2" | Black | 125 | 13 | 1625 | 5-15P | Straight | 45 | 0.7 | 32 | 079407315130 |
| 04949.60.10 | SJT | 3 | 16 | 9 | Gray | 125 | 13 | 1625 | 5-15P | Straight | 50 | 0.7 | 35 | 079407049493 |
| 01614.70.01 | SJT | 3 | 16 | 12 | Black | 125 | 13 | 1625 | 5-15P | Straight | 50 | 0.9 | 44 | 079407016143 |
| 01278.70.01 | SJT | 2 | 16 | 8 | Black | 125 | 13 | 1625 | 1-15P | Straight | 30 | 0.5 | 14 | 079407012787 |
| 01950.70.01 | SJT | 3 | 14 | 8 | Black | 125 | 15 | 1875 | 5-15P | Straight | 50 | 0.8 | 41 | 079407019502 |
| 600 Volt | | | | | | | | | | | | | | |
| 01951.70.01 | ST | 3 | 12 | 8 | Black | 125 | 15 | 1875 | 5-15P | Straight | 25 | 1.8 | 45 | 079407719518 |

| With Switch | CORD TYPE | NO. OF COND. | AWG SIZE | LENGTH OF CORD (FT) | COLOR OF JACKET | POWER RATING | | | NEMA CONFIG. | PLUG CONFIG. | SWITCH SPEED | PKG. PER CTN. | WT./UNIT LBS | WT./CTN. LBS | UPC CODE |
|-------------|-----------|--------------|----------|---------------------|-----------------|--------------|------|-------|--------------|--------------|------------------|---------------|--------------|--------------|--------------|
| | | | | | | VOLTS | AMPS | WATTS | | | | | | | |
| 01732.70.01 | SJT | 3 | 18 | 8 | Black | 125 | 10 | 1250 | 5-15P | Straight | 1 Speed (On/Off) | 25 | 0.7 | 18 | 079407017324 |
| 02053.70.01 | SJT | 3 | 18 | 12 | Black | 125 | 10 | 1250 | 5-15P | Straight | 1 Speed (On/Off) | 15 | 0.8 | 12 | 079407020539 |

| With Strain Relief | CORD TYPE | NO. OF COND. | AWG SIZE | LENGTH OF CORD (FT) | COLOR OF JACKET | POWER RATING | | | NEMA CONFIG. | PLUG CONFIG. | STRAIN RELIEF | PKG. PER CTN. | WT./UNIT LBS | WT./CTN. LBS | UPC CODE |
|--------------------|-----------|--------------|----------|---------------------|-----------------|--------------|------|-------|--------------|--------------|------------------|---------------|--------------|--------------|--------------|
| | | | | | | VOLTS | AMPS | WATTS | | | | | | | |
| 02548.70.01 | SJT | 3 | 16 | 6 | Black | 125 | 13 | 1625 | 5-15P | Straight | 7" From Free End | 25 | 0.5 | 13 | 079407025480 |

| With Receptacle Only | CORD TYPE | NO. OF COND. | AWG OF CORD SIZE | LENGTH OF CORD (FT) | COLOR OF JACKET | POWER RATING | | | NEMA CONFIG. | RECEPTACLE CONFIG. | PKG. PER CTN. | WT./UNIT LBS | WT./CTN. LBS | UPC CODE |
|----------------------|-----------|--------------|------------------|---------------------|-----------------|--------------|------|-------|--------------|--------------------|---------------|--------------|--------------|--------------|
| | | | | | | VOLTS | AMPS | WATTS | | | | | | |
| 04530.73.01 | SJT | 3 | 16 | 3 | Black | 125 | 13 | 1625 | 5-15R | Straight | 50 | 0.2 | 9 | 079407045303 |

Product Construction:

Conductor:

- 18 AWG through 12 AWG stranded bare copper per ASTM B174

Insulation:

- Premium-grade, color-coded PVC

Jacket:

- PVC; black or gray

Applications:

- For replacement use

Features:

- Straight plug
- Conductor stripped 5/8"
- Jacket removed 11/2"

Industry Approvals:

- UL Listed
- CSA



Range Cords

Type SRDT • 50 Amps • 60° C • 300 Volts

| CATALOG NUMBER | NO. OF COND. | AWG SIZE | LENGTH OF CORD (FT) | COLOR OF JACKET | POWER RATING | | | NEMA CONFIG. | PKG. PER CTN. | WT./ UNIT LBS | WT./ CTN. LBS | UPC CODE |
|----------------|--------------|-----------|---------------------|-----------------|--------------|------|-------|--------------|---------------|---------------|---------------|--------------|
| | | | | | VOLTS | AMPS | WATTS | | | | | |
| 05604.63.10 | 3 | 2#6 & 1#8 | 4 | Gray | 250 | 50 | 12500 | 10-50P | 12 | 1.8 | 22 | 079407056040 |
| 05606.63.10 | 3 | 2#6 & 1#8 | 6 | Gray | 250 | 50 | 12500 | 10-50P | 12 | 2.6 | 31 | 079407056064 |
| 00604.63.01 | 4 | 2#6 & 2#8 | 4 | Black | 250 | 50 | 12500 | 14-50P | 12 | 2.2 | 27 | 079407006045 |
| 00606.63.01 | 4 | 2#6 & 2#8 | 6 | Black | 250 | 50 | 12500 | 14-50P | 6 | 3.2 | 19 | 079407006069 |



Product Construction:

Conductor:

- 8 AWG through 6 AWG stranded bare copper per ASTM B174

Insulation:

- Premium-grade PVC; black or gray

Applications:

- Ranges in homes built prior to 1997 (3-conductor)
- Ranges in homes built after 1997 (4-conductor)

Features:

- Right-angle cap
- Eyelet ends for safer hookups
- Strain-relief clamp protects cord from damage caused by pulling or stretching

Industry Approvals:

- UL Listed

Dryer Cords

Type SRDT • 30 Amps • 60° C • 300 Volts

| CATALOG NUMBER | NO. OF COND. | AWG SIZE | LENGTH OF CORD (FT) | COLOR OF JACKET | POWER RATING | | | NEMA CONFIG. | PKG. PER CTN. | WT./ UNIT LBS | WT./ CTN. LBS | UPC CODE |
|----------------|--------------|----------|---------------------|-----------------|--------------|------|-------|--------------|---------------|---------------|---------------|--------------|
| | | | | | VOLTS | AMPS | WATTS | | | | | |
| 05654.63.10 | 3 | 3#10 | 4 | Gray | 250 | 30 | 7500 | 10-30P | 12 | 1.2 | 14 | 079407056545 |
| 05656.63.10 | 3 | 3#10 | 6 | Gray | 250 | 30 | 7500 | 10-30P | 12 | 1.5 | 18 | 079407056569 |
| 01004.63.01 | 4 | 4#10 | 4 | Black | 250 | 30 | 7500 | 14-30P | 12 | 1.5 | 18 | 079407010042 |
| 01006.63.01 | 4 | 4#10 | 6 | Black | 250 | 30 | 7500 | 14-30P | 6 | 2.1 | 12 | 079407010066 |



Product Construction:

Conductor:

- 10 AWG stranded bare copper per ASTM B174

Insulation:

- Premium-grade, color-coded PVC

Jacket:

- PVC; black or gray

Applications:

- Dryers in homes built prior to 1997 (3-conductor)
- Dryers in homes built after 1997 (4-conductor)

Features (cont'd):

- Strain-relief clamp protects cord from damage caused by pulling or stretching

Industry Approvals:

- UL Listed
- Meets revised 1997 NEC requirements

Air Conditioner Replacement Cords

3-Conductor Grounded • Type SPT-3 • 60° C • 300 Volts

| CATALOG NUMBER | NO. OF COND. | AWG SIZE | LENGTH OF CORD (FT) | COLOR OF JACKET | POWER RATING | | | PLUG CONFIG. | NEMA CONFIG. | PKG. PER CTN. | WT./ UNIT LBS | WT./ CTN. LBS | UPC CODE |
|----------------|--------------|----------|---------------------|-----------------|--------------|------|-------|--------------|--------------|---------------|---------------|---------------|--------------|
| | | | | | VOLTS | AMPS | WATTS | | | | | | |
| 04194.60.17 | 3 | 14 | 3 | Beige | 125 | 15 | 1875 | Straight | 5-15P | 24 | 0.3 | 8 | 079407041947 |
| 04195.60.17 | 3 | 14 | 6 | Beige | 125 | 15 | 1875 | Straight | 5-15P | 24 | 0.6 | 15 | 079407041657 |
| 04199.60.17 | 3 | 12 | 6 | Beige | 250 | 20 | 5000 | Right Angle | 6-20P | 24 | 0.9 | 22 | 079407041992 |



Product Construction:

Conductor:

- 12 AWG and 14 AWG stranded bare copper per ASTM B174

Insulation:

- Premium-grade, color-coded PVC

Jacket:

- PVC; beige

Applications:

- For replacement use with air conditioners

Features:

- Conductor stripped 5/8"
- Free end slit 1 1/2"

Industry Approvals:

- UL Listed



Major Appliance Cords

3-Conductor Grounded • Type SPT-3 • 15 and 20 Amps • 60° C • 300 Volts

| CATALOG NUMBER | NO. OF COND. | AWG SIZE | LENGTH OF CORD (FT) | COLOR OF JACKET | POWER RATING | | | NEMA CONFIG. | PKG. PER CTN. | WT./UNIT LBS | WT./CTN. LBS | UPC CODE |
|----------------|--------------|----------|---------------------|-----------------|--------------|------|-------|--------------|---------------|--------------|--------------|--------------|
| | | | | | VOLTS | AMPS | WATTS | | | | | |
| 00436.63.17 | 3 | 14 | 6 | Beige | 125 | 15 | 1875 | 5-15P/5-15R | 24 | 0.6 | 15 | 079407004362 |
| 00439.63.17 | 3 | 14 | 9 | Beige | 125 | 15 | 1875 | 5-15P/5-15R | 24 | 0.9 | 21 | 079407004393 |
| 00442.63.17 | 3 | 14 | 12 | Beige | 125 | 15 | 1875 | 5-15P/5-15R | 12 | 1.2 | 14 | 079407004423 |
| 00762.63.17 | 3 | 12 | 9 | Beige | 250 | 20 | 5000 | 6-20P/6-20R | 24 | 1.4 | 34 | 079407007622 |
| 00772.63.17 | 3 | 12 | 9 | Beige | 125 | 20 | 2500 | 5-20P/5-20R | 24 | 1.4 | 34 | 079407007721 |



Product Construction:

Conductor:

- 12 and 14 AWG stranded bare copper per ASTM B174

Insulation:

- Premium-grade PVC; beige

Applications:

- Air conditioners
- Refrigerators
- Freezers
- Microwaves
- Dehumidifiers

Features:

- Molded right-angle plug

Industry Approvals:

- UL Listed

Power Supply Replacement Cords

3-Conductor Grounded • Types SPT-1 and SPT-3 • 60° C • 300 Volts

| CATALOG NUMBER | CORD TYPE | NO. OF COND. | AWG SIZE | LENGTH OF CORD (FT) | COLOR OF JACKET | POWER RATING | | | NEMA CONFIG. | PLUG CONFIG. | PKG. PER CTN. | WT./UNIT LBS | WT./CTN. LBS | UPC CODE |
|----------------|-----------|--------------|----------|---------------------|-----------------|--------------|------|-------|--------------|--------------|---------------|--------------|--------------|--------------|
| | | | | | | VOLTS | AMPS | WATTS | | | | | | |
| 02050.70.10 | SPT-1 | 3 | 18 | 8 | Gray | 125 | 10 | 1250 | 5-15P | Straight | 50 | 0.4 | 21 | 079407020508 |
| 02522.73.01 | SPT-3 | 3 | 16 | 6 | Black | 125 | 13 | 1625 | 5-15P | Straight | 25 | 0.6 | 14 | 079407025220 |
| 04106.73.10 | SPT-3 | 3 | 16 | 6 | Gray | 125 | 13 | 1625 | 5-15P | Right Angle | 50 | 0.4 | 22 | 079407041060 |
| 04103.73.10 | SPT-3 | 3 | 16 | 3 | Gray | 125 | 13 | 1625 | 5-15P | Right Angle | 100 | 0.3 | 26 | 079407041039 |
| 04806.73.10 | SPT-3 | 3 | 16 | 6 | Gray | 125 | 13 | 1625 | 5-15P | Straight | 50 | 0.4 | 19 | 079407048069 |
| 04803.73.10 | SPT-3 | 3 | 16 | 3 | Gray | 125 | 13 | 1625 | 5-15P | Straight | 100 | 0.3 | 27 | 079407048038 |



Product Construction:

Conductor:

- 18 AWG and 16 AWG stranded bare copper per ASTM B174

Insulation:

- Premium-grade, color-coded PVC

Jacket:

- PVC; black, gray or beige

Applications:

- For replacement use

Features:

- Conductor stripped 5/8"
- Free end slit 1 1/2"

Industry Approvals:

- UL Listed