


TELECOM PRODUCT LINE

Loose tube, ribbon, drop, and specialty cables




Loose Tube Cables




	Product Family	Family P/N GEL TUBES	Family P/N DRY	Sheath Design	Fiber Count
1	LT 2.0™	E2G1JKT	E2D1JKT	All-Dielectric	4-456
		E2G1A1J	E2D1A1J	SA/SJ	4-456
		E2G1A2J	E2D1A2J	SA/DJ	4-456
		E2G2A2J	E2D2A2J	DA/DJ	4-288
		E2G2A3J	E2D2A3J	DA/TJ	4-288
2	ExpressLT™	E2GNA2J	E2DNA2J	Dual Jacket NA	4-288
		ETH1JKT	EDH1JKT	All-Dielectric	4-432
		ETH1A1J	EDH1A1J	SA/SJ	4-432
		ETH1A2J	EDH1A2J	SA/DJ	4-432
		ETH2A2J	EDH2A2J	DA/DJ	4-288
		ETH2A3J	EDH2A3J	DA/TJ	4-288
3	CentralLT 600	ETHNA2J	EDHNA2J	Dual Jacket NA	4-288
		ETHDA2J	EDHDA2J	Dielectric Armor	4-288
4	MicroUnitube™	C6H1A1J	D6H1A1J	SA/SJ	2-12
		UMH1JKT	--	All-Dielectric	2-12
		UMR1A1J	--	SA/SJ	2-24

OSP Ribbon Cables



	Product Family	Sheath Design	Family P/N GEL TUBE	Family P/N DRY TUBE	Fiber Count
Flat/Conventional Ribbon					
1	FusionLink™ RICT (Gel)	All-Dielectric	RCG1JKT	--	12-864
		SA/SJ	RCG1A1J	--	12-864
	Dry FusionLink™ RICT (Coupled)	All-Dielectric	--	RCD1JKT	60-432, 612-864
		SA/SJ	--	RCD1A1J	60-432, 612-864
Dry FusionLink™ RICT (Uncoupled)	All-Dielectric	--	RCU1JKT	12-48, 576	
	SA/SJ	--	RCU1A1J	12-48, 576	
2	MassLink™ Multi-Tube Ribbon	All-Dielectric	RLG1JKT	--	288-1728
		SA/SJ	RLG1A1J	--	288-1728
		SA/DJ	RLG1A2J	--	288-432
FlexRibbon® Technology					
1	FusionLink™ RICT with FlexRibbon® Technology	All-Dielectric	--	RCF1JKT	250µm fiber 96-432
		SA/SJ	--	RCF1A1J	250µm fiber 96-432
		All-Dielectric	--	RCF1JKT	200µm fiber 288-432
2	MassLink™ Multi-Tube with FlexRibbon® Technology	All-Dielectric	--	RLF1JKT	250µm fiber 432-1728
		SA/SJ	--	RLF1A1J	250µm fiber 432-864
		SA/DJ	--	RLF1A2J	250µm fiber 1728
		All-Dielectric	--	RLF1W1JKT	200µm fiber 576-1728
		All-Dielectric	--	RLF2F1JKT	200µm fiber 3456
		All-Dielectric	--	RLF1JKT	200µm fiber 6912

Drop Cables



	Product Family	Sheath Design	Family P/N GEL TUBES	Family P/N DRY	Fiber Count
1	ResiLink™ Flat Drop	A Dielectric	DFD1JKT	--	1-24
		B Toneable	DFDNATJ	--	1-24
2	ResiLink™ Universal Service Drop	A Dielectric	D3D1JKT	--	1
		B Toneable	D3DNATJ	--	1
2	ResiLink™ 36/48 Flat Drop	A Dielectric	DFD1JKT-24	--	36 & 48
		B Toneable	DFDNATJ-24	--	36 & 48
3	Central LT 300	SA/SJ, with Ripcords	C3R1AJ	D3R1AJ	1-12
		SA/SJ, w/o Ripcords	C3H1AJ	D3H1AJ	1-12
4	ezDrop™ Figure 8	Non-Armored	DF81JKT	--	1-6
1	FlexDrop™ Flat Drop with FlexRibbon® Technology	A Dielectric	--	RFD1JKT	12 & 24

MicroDuct Cable Solutions



A 432-count Sirocco^{HD} cable has a diameter similar to a pencil and will fit a 10mm ID microduct.

	Product Family	Minimum Micro Duct ID (mm)	Family P/N GEL TUBES	Family P/N DRY	Fiber Count
1	Sirocco™ 250 μm Fiber	8	MDM1JKT-12	--	12-72
		8	MDM1JKT-12	--	12-72
		8	MDM1JKT-12	--	12-72
		8	MDM1JKT-12	--	12-72
		10	MDM1JKT-12	--	96
		10	MDM1JKT-24	--	120-144
		12	MDM1JKT-12	--	108-144
1	Sirocco ^{HD} 200 μm Fiber	7	MDH1JKT-12	--	96
		8	MDH1JKT-12	--	144
		8	MDH1JKT-24	--	192
		10	MDH1JKT-12	--	288
		10	MDH1JKT-24	--	288
		10	MDH1JKT-24	--	432
		14	MDH1JKT-36	--	864




	Product Family	Sheath Design	Family P/N GEL TUBES	Family P/N DRY	Fiber Count
1	ezMicroDuct™ with 250 μm FlexRibbon® Technology	≥ 13 mm ID duct	--	RCFMD1JKT	144-192
1	ezMicroDuct™ with 200 μm FlexRibbon® Technology	≥ 12 - 16 mm ID duct	--	RCFMDS1JKT	288 - 864





	Product Family	Sheath Design	Family P/N GEL TUBES	Family P/N DRY	Fiber Count
1	FlexDrop™ with FlexRibbon® Technology	≥ 4 mm ID duct	--	RRD1JKT	12 & 24

Aerial Self-Support Cables



	Product Family	Sheath Design	Family P/N GEL TUBES	Family P/N DRY	Fiber Count
1	AeroLink™ Figure 8	All-Dielectric	F8A1JKT	F8D1JKT	12-216
		SA/SJ	F8A1AIJ	F8D1AIJ	12-216
2	ADSS EZSPAN™ Span	Single Jacket	ADES	ADFS	6-144
		Dual Jacket	ADED	--	6-144
3	ADSS Long Span	Single Jacket	ADLS	--	6-432
		Dual Jacket	ADLD	--	6-432
		Track Resistant Jacket	ADLT	--	6-432

Indoor/Outdoor Cables







	Product Family	Sheath Design	Family P/N	Flame Rating	Fiber Count
1	Indoor/Outdoor ezDistribution™	A Single Jacket, Non-Unitized	C1181-00	Riser	2 to 24
		B Interlock Armor	C1181AJ-00	Conductive Riser	2 to 24
		A Single Jacket, Unitized	C1181-12	Riser	24 to 144
		C Interlock Armor	C1181AJ-12	Conductive Riser	24 to 144
		A LSZH Single Jacket, Non-Unitized	700-00	Riser - LS	2 to 24
		B LSZH Interlock Armor	700AJ-00	Conductive Riser - LS	2 to 24
		A Single Jacket, non-unitized	C1182-00	Plenum	2 to 24
		B Interlock Armor	C1182AJ-00	Conductive Plenum	2 to 24
		A Single Jacket, unitized	C1182-12	Plenum	24 to 96
		C Interlock Armor	C1182AJ-12	Conductive Plenum	24 to 96
2	Indoor/Outdoor CampusLink™ Stranded Loose Tube Gel-Filled Tubes	A Single Jacket	DRLTB-12	Riser	2 to 144
		A Double Jacket	DRLTC-12	Riser	2 to 144
		B Double Jacket with Corrugated Steel Armor	DRLTD-12	Conductive Riser	2 to 144
		B Interlock Armor	DRLTBAJ-12	Conductive Riser	2 to 144
2	Indoor/Outdoor CampusLink™ Stranded Loose Tube Gel-Free Tubes	A Single Jacket	DRLDB-12	Riser	2 to 288
		A Double Jacket	DRLDC-12	Riser	2 to 144
		B Double Jacket with Corrugated Steel Armor	DRLDD-12	Conductive Riser	2 to 144
		B Interlock Armor	DRLDBAJ-12	Conductive Riser	2 to 288
		A Single Jacket	DPLDB-12	Plenum	2 to 144
		B Interlock Armor	DPLDBAJ-12	Conductive Plenum	2 to 144
3	Indoor/Outdoor CampusLink™ Central Loose Tube Gel-Free Tube	Single Jacket	DRLDB-00	Riser	2 to 12
		Interlock Armor	DRLDBAJ-00	Conductive Riser	2 to 12
		LSZH - Single Jacket	DDLSZHB-00	Riser	2 to 12
		LSZH - Interlock Armor	DDLSZHBAJ-00	Conductive Riser	2 to 12
		Single Jacket	DPLDB-00	Plenum	2 to 12
		Interlock Armor	DPLDBAJ-00	Conductive Plenum	2 to 12

MFC Cables (Indoor Only)



Product Family	Sheath Design	Family P/N	Unit Size	Units	Flame Rating	Fiber Count
1 Micro Fiber Cable	Single Jacket	MFC14	1.4 mm	12f - Multi	Plenum	12-48
	Single Jacket	MFCL14	1.4 mm	12f - Multi	LSZH Riser	12-48
	Single Jacket	MFC20	2 mm	Single Unit	Plenum	8-12
	Single Jacket	MFC20	2 mm	8 or 12f - Multi	Plenum	8-216
	Interlock Armor	MFC20AJ	2 mm	8 or 12f - Multi	Plenum	8-144
	Single Jacket	MFC30	3 mm	Single Unit	Plenum	8-24
	Interlock Armor	MFC30AJ	3 mm	Single Unit	Plenum	8-24
	Single Jacket	MFC	3 mm	Single Unit	Plenum	8-12
	Single Jacket	MFC	3.8 mm	Single Unit	Plenum	16-24
	Single Jacket	MFC	3 mm	8 or 12f - Multi	Plenum	8-72
	Interlock Armor	MFCAJ	3 mm	8 or 12f - Multi	Plenum	8-72
	Double Jacket	MFCDJ	3 mm	Single Unit	Plenum	8-12
	Single Jacket	MFCL	3 mm	Single Unit	LSZH Riser	8-12
	Single Jacket	MFCL	3.8 mm	Single Unit	LSZH Riser	16-24
	Single Jacket Zipcord	MFCZ	3 mm	2 x 12f	Plenum	16-24
	Single Jacket	MFC36	3.6 mm	Single Unit	Plenum	16-24
Single Jacket	MFCL36	3.6 mm	Single Unit	Plenum	16-24	

Specialty Cables




Product Family	Sheath Design	Family P/N	Tube	Indoor/Outdoor	Flame Rating	Fiber Count
1 Airguard™ XP Oil & Gas Chemical Resistant	Double Jacket All-Dielectric	XPRLTM	Gel-Filled	yes	OFNG-ST1/FT4 ST1	2 to 288
	Single Jacket	XPRLTMB	Gel-Filled	yes	OFN	2 to 216
	Double Jacket Single Armor	XPRLTMD	Gel-Filled	yes	OFNG-ST1/FT4 ST1	2 to 288
2 Industrial LSZH	Double Jacket All-Dielectric	IRZHC	Gel Free	yes	OFNR-ST1/FT4 ST1	1 to 288
	Single Jacket	IRZHB	Gel Free	yes	OFNG-ST1/FT4 ST1	1 to 288
	Double Jacket Single Armor	IRZHD	Gel Free	yes	OFNR-ST1/FT4 ST1	1 to 288
	Double Jacket Interlock Armor	IRZHBAJ	Gel Free	yes	OFNG-ST1/FT4 ST1	1 to 288
3 Mining	Double Jacket All-Dielectric	RLTM	Gel-Filled	yes	OFNR/FT4	2-144
4 Transit	Single Jacket	DDLSZHB	Gel Free	yes	OFNG-ST1/FT4 ST1	1 to 288
	Double Jacket All-Dielectric	DDLSZHC	Gel Free	yes	OFNR-ST1/FT4 ST1	1 to 288
	Single Jacket Single Armor	DDLSZHE	Gel Free	yes	OFNG-ST1/FT4	1 to 288
	Double Jacket Interlock Armor	DDLSZHBAJ	Gel Free	yes	OFNG-ST1/FT4 ST1	1 to 288
5 Pipeline Sensing	Custom	EDS	Gel Free	OSP Only	NA	Custom
	Custom	ETS	Gel-Filled	OSP Only	NA	Custom
6 FAA/Airport	Double Jacket	FAACF	Gel-Filled	OSP Only	NA	2 to 60

Indoor & Indoor/Outdoor Ribbon Cables

Product Family	Sheath Design	Family P/N	Tube	Indoor or Indoor/Outdoor	Flame Rating	Fiber Count
----------------	---------------	------------	------	--------------------------	--------------	-------------

Flat/Conventional Ribbon

1	COLink™ Ribbon Central Tube	Single Jacket	RRCDK	Dry	Indoor	Riser	12-864
		Interlock Armor	RRCDKAJ	Dry	Indoor	Riser	12-864
		Single Jacket	RPCDK	Dry	Indoor	Plenum	12-144
2	FusionLink™ I/O Ribbon Central Tube	Single Jacket	RRIODCK	Dry	Indoor/Outdoor	Riser	12-864
		Interlock Armor	RRIODKAJ	Dry	Indoor/Outdoor	Riser	12-864
		Single Jacket	RZIODCK	Dry	Indoor/Outdoor	LSZH	12-144
		Interlock Armor	RZIODKAJ	Dry	Indoor/Outdoor	LSZH	12-144
		Single Jacket	RRCTK	Gel	Indoor/Outdoor	Riser	12-864
		Interlock Armor	RRCTKAJ	Gel	Indoor/Outdoor	Riser	12-864
3	COLink™ Multi-Tube Ribbon	Single Jacket	RRLDK	Dry	Indoor	Riser	144-576
		Interlock Armor	RRLDKAJ	Dry	Indoor	Riser	144-576
4	MassLink™ I/O Multi-Tube Ribbon	Single Jacket	RRLTK	Gel	Indoor/Outdoor	Riser	288-432
		Interlock Armor	RRLTKAJ	Gel	Indoor/Outdoor	Riser	288-432
		Single Jacket	RZLTK	Gel	Indoor/Outdoor	LSZH	288-432
		Interlock Armor	RZLTKAJ	Gel	Indoor/Outdoor	LSZH	288-432






Indoor & Indoor/Outdoor FlexRibbon® Technology

2	FusionLink Ribbon Central Tube	Single Jacket	RRIOCFK	Dry	Indoor/Outdoor	Riser	200µm fiber 288-432
1	FusionLink Ribbon Central Tube	Single Jacket	RRCFK	Dry	Indoor	Riser	200µm fiber 288-432
4	MassLink™ Multi-Tube with FlexRibbon® Technology	Single Jacket	RRIOLFK	Dry	Indoor/Outdoor	Riser	250µm fiber 864-1728
		Single Jacket	RRIOLFK	Dry	Indoor/Outdoor	Riser	200µm fiber 864-1728
		Single Jacket	RZIOFLK	Dry	Indoor/Outdoor	LSZH	250µm fiber 1152-1728
		Single Jacket	RRZLFK	Dry	Indoor/Outdoor	LSZH	200µm fiber 864
		Single Jacket	RRZLFWK	Dry	Indoor/Outdoor	LSZH	200µm fiber 1728
3	MassLink™ Multi-Tube with FlexRibbon® Technology	Single Jacket	RRLFK	Dry	Indoor	Riser	250µm fiber 864-1728
		Single Jacket	RRLFK	Dry	Indoor	Riser	200µm fiber 864-1728
		Single Jacket	RZLFLK	Dry	Indoor	LSZH	250µm fiber 1152-1728
		Single Jacket	RRZIOFLK	Dry	Indoor/Outdoor	LSZH	200µm fiber 864
		Single Jacket	RRZIOFLWK	Dry	Indoor/Outdoor	LSZH	200µm fiber 1728
5	ezMicroDuct with FlexRibbon® Technology	Single Jacket	RRIOCFKMD	Dry	Indoor/Outdoor	Riser	200µm fiber 288
		Single Jacket	RRCFKMD	Dry	Indoor	Riser	200µm fiber 288

Indoor Tight Buffer Cables



	Product Family	Sheath Design	Family P/N	Flame Rating	Fiber Count	
1	ezInterconnect™	Simplex	516/520/529	Riser	1	
			816/820/829	Plenum	1	
			LSZH16/LSZH20/LSZH29	Riser - Low Smoke	1	
2		Zipcord		516Z/520Z/529Z	Riser	2
				816Z/820Z/829Z	Plenum	2
				LSZH16Z/LSZH20Z/LSZH29Z	Riser - Low Smoke	2
1		Duplex		529R	Riser	2
				829R	Plenum	2
1		Quadplex		548R	Riser	4
	848R			Plenum	4	



	Product Family	Sheath Design	Family P/N	Flame Rating	Fiber Count
1	Indoor ezDistribution™	Single Jacket, Non-Unitized	400-00	Riser	2 to 24
3		Interlock Armor	400AJ-00	Conductive Riser	2 to 24
2		Single Jacket, Unitized	400-12	Riser	24 to 144
4		Interlock Armor	400AJ-12	Conductive Riser	24 to 144
1		LSZH Single Jacket, Non-Unitized	600-00	Riser - LS	2 to 24
3		LSZH Interlock Armor	600AJ-00	Conductive Riser - LS	2 to 24
2		LSZH Single Jacket, Unitized	600-12	Riser - LS	24 to 144
4		LSZH Interlock Armor	600AJ-12	Conductive Riser - LS	24 to 144
1		Single Jacket, Non-Unitized	800-00	Plenum	2 to 24
3		Interlock Armor	800AJ-00	Conductive Plenum	2 to 24
2		Single Jacket, Unitized	800-12	Plenum	24 to 96
4		Interlock Armor	800AJ-12	Conductive Plenum	24 to 96
5	Indoor Breakout	Single Jacket, Unitized	525	Riser	2 to 36
		Single Jacket, Unitized	516	Riser	2 to 12
		Single Jacket, Unitized	LSZH25	Riser	2 to 36
		Single Jacket, Unitized	825	Plenum	2 to 36



na.prysmian.com

TLS-0001-0224

Follow us

