

Specialty Products Line Card

Custom designs are available; contact your Sales Representative or visit na.prysmian.com for additional product information.



FIRE PROTECTION



UL 2196 2-Hour RHW-2 in EM




UL 2196 2-Hour RHW-2 in XW Breathsaver® Phenolic Conduit



UL 2196 2-Hour MC or ULC-S139 2-Hour RC90



UL 2196 2-Hour MC or ULC-S139 2-Hour RC90 LSZH Jacket



IEC 60331-25 Fire Resistant QFCI Loose Tube Fiber Optic



LIGHTING



Colorable FAA-L-824 Type C



Triple Rated MV-90 FAA Type C & CSA



FAA-L-824 Type B Airport Lighting Power



Type RHH/RHW-2/USE-2 Insulated Wire



Power Duct® Cable in Conduit

TRANSIT



600V AREMA NFPA 130 & 502 LSZH Control



2.4kV NFPA 130 LSZH MV-90 Traction Power



600V NFPA 130 & 502 LV LSZH XHHW-2



600V and 2kV NFPA 130 & 502 LSZH RHW-2




2.4kV-35kV NFPA 130 MV-90 & MV-105



AREMA Signal – Armored Aerial, Underground Railroad, Underground and Track Wire

BRIDGE



Aerial



Riser and Droop (Traveling)



Submarine



Prysmian North America
4 Tesseneer Drive, Highland Heights, KY 41076
na.prysmian.com
SPL-0002-0424

Specialty Products Line Card

Custom designs are available; contact your Sales Representative or visit na.prysmian.com for additional product information.



NUCLEAR



ULTROL® 60+ SIS Switchboard Wire
(Class K and H)



ULTROL® 60+ Power Cable



ULTROL® 60+ Thermocouple Extension Cable



ULTROL® 60+ Instrumentation Cable



ULTROL® 60+ Control Cable



ULTROL® 60+ Low-Voltage Power Cable



ULTROL® 60+ Medium-Voltage Power Cable


WIRELESS



Ecosafe™ CO II



Ecosafe™ CO III and IV



4G/5G Hybrid+ Discrete

DEFENSE



SWF Type Shipboard Cable (MIL-915)



Silicone High Voltage Cable



MWF Type Shipboard Cable (MIL-915)



Field Deployable Tactical Breakout Cable



Field Deployable Tactical Distribution Cable



SS Type Hydrophone Cable (MIL-915)



LSZH Fiber Optic Shipboard Cable (MIL-85045)

RENEWABLES



SunGen® Copper Photovoltaic Wire



Aluminum Wind 2KV XL-CPE TYPE RHH OR RHW-2



Prysmian North America
4 Tesseneer Drive, Highland Heights, KY 41076
na.prysmian.com
SPL-0002-0424

Specialty Products Line Card

Custom designs are available; contact your Sales Representative or visit na.prysmian.com for additional product information.




CRANE



ALL-TEMP INDUSTRIRITE® Type W & SOW



AUTO-FLEX® Tray-Rated Power




FLAT-FLEX® Power & Control



FIBER-FLEX® Optical Fiber Festooning



BOSTFLEX® Control



AUTO-FLEX® TCP Flexible TC-ER Power Supply/Drop



INDUSTRIRITE® Portable Power for Welding

CRANE (Cont.)



CORDAFLEX® Low Voltage Reeling



CORDAFLEX® Low Voltage Vertical Reeling



PROTOCOLON® Medium Voltage Reeling (Round or Flat)



SPREADERFLEX® Low Voltage Basket Operation



RONDOFLEX® Low Voltage Festoon Operation (Round or Flat)



RONDOFLEX® Low Voltage Chain Operation



OPTOFLEX® Data Transmission



Specialty Products Line Card

Custom designs are available; contact your Sales Representative or visit na.prysmian.com for additional product information.




IRRIGATION



Superseal Self-Repairing Direct Burial



Supertuf Direct Burial



Power and Control Cable



Powerduct Cable In-Conduit



Span and Motor Lead Cable



Armored Perimeter Cable

ROLLING STOCK



Polyrad™ XT



Polyrad™ ULTRA



Category 5e Shielded Cable



Polyrad™ XT Transit Data Communications

ROLLING STOCK



Diesel Locomotive



Electronically Controlled Pneumatic (ECP) Brake



TRANSPower Head-End Power (HCP)

MINING



Anaconda® Brand Lead-Cured Mining-Grade Types W, G, or G-GC (2KV)




Anaconda® Brand Lead-Cured Mining-Grade Type SHD (2KV to 35KV)



Anaconda® Brand Mine Power Feeder (5kv to 35KV)



BOSTMINE® Mold-Cured Mining-Grade



BOSTREEL® Power Reeling



Prysmian North America
4 Tesseneer Drive, Highland Heights, KY 41076
na.prysmian.com
SPL-0002-0424