

Single Jacketed Buried Service Wire

Spec. 3502

BELL SYSTEM TYPE C SERVICE

Product Construction:**Conductors:**

- 22 AWG solid annealed copper

Insulation:

- High density polyethylene

Pairing:

- Varying pair lays

Core Filling:

- 80°C filling and flooding compounds

Core Wrap:

- Polyester tape

Shield:

- 0.004" corrugated commercial bronze or copper-clad steel tape

Rip Cord:

- Under the jacket

Jacket:

- Black, linear low density polyethylene

Application(s):

- Intended for use in buried service application to the subscriber loops

Compliances:

- Telcordia (Bellcore) Specification GR-3163-CORE
- RoHS Compliant (effective 1/1/10)

Packaging:

- Non-returnable plywood reels in lengths as shown above

**Nominal Cable Data**

| CATALOG NUMBER | PAIRS AWG | | O.D. (INCHES) | WEIGHT (LBS/MFT) | STANDARD LENGTH (FT) |
|----------------|-----------|----|---------------|------------------|----------------------|
| 2095160 | 3 | 22 | 0.30 | 55 | 1200 |
| 2095084 | 3 | 22 | 0.30 | 55 | 3000 |
| 2095086 | 3 | 22 | 0.30 | 55 | 5000 |
| 2095161 | 6 | 22 | 0.37 | 77 | 800 |
| 2095098 | 6 | 22 | 0.37 | 77 | 3000 |
| 2095099 | 6 | 22 | 0.37 | 77 | 5000 |

Data subject to change without notice. Contact your Customer Service Representative for latest information.