

High Visibility All Weather Extension Cords

3-Conductor Grounded • Type SJE00W • -50 °C to 105 °C • 300 Volts

CATALOG NUMBER	NO. OF COND.	AWG SIZE	LENGTH OF CORD (FT)	COLOR OF JACKET	POWER RATING			PKG. PER CTN.	WT./ UNIT LBS	WT./ CTN. LBS	UPC CODE
					VOLTS	AMPS	WATTS				
03685.61.05	3	10	50	Yellow	125	15	1875	2	12.5	25	079407036851
03686.61.05	3	10	100	Yellow	125	15	1875	2	24.5	49	079407036868

Product Construction:

Conductor:

- 10 AWG stranded bare copper per ASTM B174

Insulation:

- Premium-grade, color-coded premium PVC

Jacket:

- TPE; yellow
- Temperature range: -50 °C to 105 °C
- Voltage rating: 300 volts

NEMA Configuration:

- 5-15P/5-15R

Applications:

- Heavy construction equipment
- Air compressors
- Circular saws
- Generators

Industry Approvals:

- UL Listed
- OSHA Acceptable

