

Plastic Guard Utility Light

3-Conductor Grounded • Type SJT • 300 Volts

CATALOG NUMBER	NO. OF COND.	AWG SIZE	LENGTH OF CORD (FT)	COLOR OF JACKET	POWER RATING			PKG. PER CTN.	WT./ UNIT LBS	WT./ CTN. LBS	UPC CODE
					VOLTS	AMPS	WATTS				
04497.60.05	3	16	50	Yellow	125	13	1650	6	3.5	21	079407044979

While Supplies Last



Product Construction:

Conductor:

- 16 AWG stranded bare copper per ASTM B174

Insulation:

- Premium-grade, color-coded PVC

Jacket:

- PVC; yellow
- Voltage rating: 300 volts

Applications:

- Temporary lighting
- For general use only
- Not for use in hazardous locations

Features:

- Side outlet
- On/off switch
- 75-watt bulb maximum
- Swivel hook
- Polypropylene guard

Industry Approvals:

- UL Listed
- OSHA Acceptable for general use