

Power Supply Replacement Cords with Switch

3-Conductor Grounded • Type SJT • 60° C • 300 Volts

CATALOG NUMBER	NO. OF COND.	AWG SIZE	LENGTH OF CORD (FT)	COLOR OF JACKET	POWER RATING			NEMA CONFIG.	SWITCH SPEED	PKG. PER CTN.	WT./ UNIT LBS	WT./ CTN. LBS	UPC CODE
					VOLTS	AMPS	WATTS						
02336.70.01	3	16	10	Black	125	13	1650	5-15P	1 Speed (On/Off)	25	0.9	22	07940743242

Product Construction:

Conductor:

- 16 AWG stranded bare copper per ASTM B174

Insulation:

- Premium-grade,color-codedPVC

Jacket:

- PVC; black

Applications:

- For replacement use
- For fan replacements

Features:

- Switch
- Straight plug
- Conductor stripped 5/8"
- Jacket removed 2"

Industry Approvals:

- UL Listed
- CSA

