

# Powr-Reel™ with 3 Outlets

3-Conductor Grounded • Type SJTW • 90 °C • 300 Volts

CATALOG NUMBER	NO. OF COND.	AWG SIZE	LENGTH OF CORD (FT)	COLOR OF JACKET	POWER RATING			PKG. PER CTN.	WT./UNIT LBS	WT./CTN. LBS	UPC CODE
					VOLTS	AMPS	WATTS				
44623.61.01	3	16	25	Yellow	125	10	1250	4	2.7	11	079407446230



**Product Construction:**

**Conductor:**

- 16 AWG stranded bare copper per ASTM B174

**Insulation:**

- Premium-grade, color-coded PVC

**Jacket:**

- PVC; yellow
- Voltage rating: 300 volts

**Applications:**

- Shop tools

**Features:**

- Tangle-Proof® instant cord storage
- Sturdy metal reel case
- 3 grounded outlets
- Cord locks in place; pull on cord to engage retractable reel

**Industry Approvals:**

- UL Listed
- OSHA Acceptable