

Safety Orange® Extension Cords

3-Conductor Grounded • Type SJTW • -40°C to 60°C • 300 Volts

CATALOG NUMBER	NO. OF COND.	AWG SIZE	LENGTH OF CORD (FT)	COLOR OF JACKET	POWER RATING			PKG. PER CTN.	WT./UNIT LBS	WT./CTN. LBS	UPC CODE
					VOLTS	AMPS	WATTS				
03318.63.04	3	16	10	Orange	125	13	1625	24	0.8	19	079407033188
03327.63.04	3	16	25	Orange	125	13	1625	24	1.8	43	079407033270
03354.63.04	3	16	50	Orange	125	13	1625	12	3.4	40	079407033546
03302.63.04	3	16	100	Orange	125	10	1250	4	6.6	26	079407033027
03328.63.04	3	14	25	Orange	125	15	1875	6	2.4	14	079407033287
03356.63.04	3	14	50	Orange	125	15	1875	4	4.6	18	079407033560
03304.63.04	3	14	100	Orange	125	13	1625	2	9.0	18	079407033041
06826.63.04	3	12	25	Orange	125	15	1875	4	3.4	14	079407068265
06853.63.04	3	12	50	Orange	125	15	1875	2	6.6	13	079407068531
06801.63.04	3	12	100	Orange	125	15	1875	2	13.0	26	079407068012



Product Construction:

Conductor:

- 16 AWG through 12 AWG stranded bare copper per ASTM B174

Insulation:

- Premium-grade, color-coded PVC

Jacket:

- PVC; orange
- Temperature range: -40°C to 60°C
- Voltage rating: 300 volts

NEMA Configuration:

- 5-15P/5-15R

Applications:

- General use indoor/outdoor cord
- Vacuum cleaners
- Floor polishers
- Sanders
- Other power equipment

Features:

- Indoor/outdoor use
- 3-conductor grounded

Industry Approvals:

- UL Listed
- OSHA Acceptable