


Einzelleitungen für Fahrzeuge

Single conductor wires

TXL

-40°C bis/up to +125°C

**LEITER:**

Kupfer blank Cu-ETP1 gem. DIN EN 13602
Symmetrischer Leiter

ISOLIERUNG:

Polyethylen, CV-vernetzt
Isolierung gem. SAE J 1128

HERSTELLERKENNZEICHNUNG:

Wenn gefordert

BESONDERE EIGENSCHAFTEN:

- Leitung gem. SAE J 1128

LIEFERART:

Lieferortabhängig

- als Ring
- im Fass
- auf NPS-Spulen

BEISPIEL FÜR BESTELLBEZEICHNUNG:

TXL AWG 16 RT

BEMERKUNGEN:

Entspricht der 2000/53/CE und 2011/65/UE RoHS
Europäischen Richtlinie

CONDUCTOR:

Annealing bare copper Cu-ETP1 acc. to DIN EN 13602
Symmetric conductor

INSULATION:

Polyethylene, CV cross-linked
Insulation acc. to SAE J 1128

MANUFACTURER IDENTIFICATION:

If requested

SPECIAL PROPERTIES:

- Wire acc. to SAE J 1128

FORM OF DELIVERY:

depending on place of delivery

- on coils
- in barrel
- on NPS-reels

EXAMPLE FOR ORDER IDENTIFICATION:

TXL AWG 16 RD

REMARKS:

In conformity with 2000/53/CE and 2011/65/UE RoHS
European Directives

Technical data

Leiter/Conductor					Leitung/Cable			
Nenn- querschnitt	Anzahl Einzeldrähte	Durchmesser Einzeldrähte	Durchmesser	Querschnitt	Isolierung Wanddicke	Außendurchmesser		Gewicht ca.
Nominal cross-section	Number of single wires	Diameter of single wires	Diameter	cross-section	Insulation wall thickness	Outside diameter		Weight approx.
AWG		max. mm	max. mm	min. mm ²	min. mm	Nom. mm	max. mm	kg/km
22	7	0,254	0,78	0,324	0,28	1,57	1,70	5,35
20	7	0,33	0,99	0,508	0,28	1,78	1,90	7,60
18	19	0,23	1,18	0,76	0,28	1,98	2,20	10,25
18	16	0,254	1,18	0,76	0,28	1,98	2,20	10,25
16	19	0,287	1,46	1,12	0,28	2,26	2,40	14,65
14	19	0,36	1,84	1,85	0,28	2,61	2,70	21,80
12	19	0,455	2,27	2,91	0,33	3,14	3,30	33,75
10	19	0,574	2,83	4,65	0,35	3,93	4,00	53,05

© PrysmianGroup 2012, All Rights Reserved

All sizes and values without tolerances are reference values. Specifications are for product as supplied by PrysmianGroup: any modification or alteration afterwards of product may give different results.

The information contained within this document must not be copied, reprinted or reproduced in any form, either wholly or in part, without the written consent of PrysmianGroup. The information is believed to be correct at the time of issue. PrysmianGroup reserves the right to amend this specification without prior notice. This specification is not contractually valid unless specifically authorised by PrysmianGroup