

Double Jacketed Buried Service Wire

Spec. 4287

WITH ALUMINUM SHIELD ICEA S-86-634

Product Construction:**Conductors:**

- Solid annealed copper

Insulation:

- High density polyethylene

Pairing:

- Varying pair lays

Core Filling:

- 80°C filling and flooding compounds

Inner Jacket:

- Linear low density polyethylene

Shield:

- Polymer-coated 0.008" aluminum tape

Rip Cord:

- Under the outer jacket

Outer Jacket:

- Black, linear low density polyethylene

Application(s):

- Intended for use in buried service application to the subscriber loops

Compliances:

- ICEA S-86-634
- RoHS Compliant (effective 1/1/10)

Packaging:

- Non-returnable plywood reels in lengths as shown above

**Nominal Cable Data**

CATALOG NUMBER	PAIRS AWG		O.D. (INCHES)	WEIGHT (LBS/MFT)	STANDARD LENGTH (FT)
2095138	2	22	0.33	51	1000
2095125	2	22	0.33	51	2500
2095126	2	22	0.33	51	5000
2095146	3	22	0.35	62	1000
2095127	3	22	0.35	62	2500
2095128	3	22	0.35	62	5000
2095137	6	22	0.41	88	1000
2095129	6	22	0.41	88	2500
2095130	6	22	0.41	88	5000
2095131	2	24	0.30	42	2500
2095132	2	24	0.30	42	5000
2095133	3	24	0.32	54	2500
2095134	3	24	0.32	54	5000
2095135	6	24	0.33	68	2500
2095136	6	24	0.33	68	5000

Data subject to change without notice. Contact your Customer Service Representative for latest information.