


Buffer Tube Slitter

Hand tool for easy mid-span access to buffer tubes



Features and Benefits

Precision Engineering

- No adjustment or tuning required
- Depth of cut is optimized for each specific tube size
- Buffer tube walls are slit open without risk of fiber damage

Rugged Construction

- Body is machined from solid aluminum
- Built for use in the real world

Recessed Blades

- Cutting surfaces are protected
- Minimal blade projection enhances tool safety

Compact and Lightweight

- Easy to transport
- Saves room in the toolkit

Clearly and Permanently Marked

- Both halves of the tool are engraved with size information
- Correct slitting direction is clearly marked
- All critical information is machined directly into the tool and cannot rub off

Heavy Duty Retaining Cord

- Keeps the two halves together for easier location and use

Buffer Tube Sizing Guides

- Allows tube dimensions to be checked without applying the tool

Quick, Safe and Easy Mid-Span Access

- Saves time, avoids injuries and protects fiber assets

Economical

- Pays for itself by avoiding dangerous work practices
- Just as effective and more durable than units costing many times more

Buffer Tube Slitter

Hand tool for easy mid-span access to buffer tubes



PART NUMBERS

Cable Design	Fiber Count	Nominal Tube OD (mm)	Part Number
ActionLink™	2 - 72	1.9	9000090000
AeroLink™ ADSS	2 - 144	2.5	9000090001
AeroLink™ fig 8	2 - 216	2.65	9000090017
AeroLink™ fig 8	2 - 216	2.5	9000090001
CampusLink™	2 - 12	4.1	9000090003
CentraLink™	2 - 12	4.1	9000090003
CentraLink™ CD	2 - 12	2.8	9000090014
Express™ LT	2- 288	2.5	9000090001
FirstLink™/FlexLink™	2 - 312	2.65	9000090017
FlexLink™ Dry	2- 288	2.8	9000090014
FusionLink™ RICT	12 - 72	6.2	9000090004
FusionLink™ RICT	84 - 96	8.4	9000090005
FusionLink™ RICT	108 - 144	9.9	9000090019
FusionLink™ RICT	156 - 216	11.0	9000090006
FusionLink™ RICT	240 - 432	14.3	9000090018
FusionLink™ RICT	456 - 576	15.4	9000090038
FusionLink™ RICT Dry	12 - 48	6.2	9000090004
FusionLink™ RICT Dry	60 - 96	9.5	9000090007
FusionLink™ RICT Dry	108 - 144	10.6	9000090010
FusionLink™ RICT Dry	156 - 216	12.3	9000090012
FusionLink™ RICT Dry	240 - 288	14.3	9000090018
FusionLink™ RICT Dry	312 - 432	15.4	9000090038
FusionLink™ RICT I/O	12 - 96	8.4	9000090005
FusionLink™ RICT I/O	108 - 216	11	9000090006
LT 2.0	4 - 456	2.0	9000090039
MassLink™ Multi-Tube Ribbon	288 - 432	6.2	9000090004
MassLink™ Multi-Tube Ribbon	444 - 864	7.9	9000090009
MassLink™ Multi-Tube Ribbon	1296 - 1728	12.1	9000090040
MassLink™ Multi-Tube Ribbon I/O	216 - 432	6.2	9000090004
MiniLink™	2 - 144	1.9	9000090000
Resilink™ ADF	1 - 12	2.8	9000090014

Spare Parts	Quantity Per Tool	Part Number
Blades (2)	2	9000090015
Retainer Cord	1	9000090008

***Note: Always check the current datasheet for the cable you are using to verify the buffer tube size prior to selecting a buffer tube slitter.**

© DRAKA & PRYSMIAN - Brands of The Prysmian Group. 2020. All Right Reserved. The information contained within this document must not be copied, reprinted or reproduced in any form, either wholly or in part, without the written consent of Prysmian Group. The information is believed correct at the time of issue. Prysmian Group reserves the right to amend any specifications without notice. These specifications are not contractually valid unless specifically authorized by Prysmian Group. Issued May 2020.