


# Tight Buffer Distribution Plenum Cable Type OFNP, CSA FT6, Indoor\*



CATALOG NUMBER	FIBER COUNT	NO. OF SUB-UNITS	NOMINAL CABLE DIAMETER		NOMINAL CABLE WEIGHT		MAXIMUM TENSILE LOAD			
			IN	MM	LBS/1000'	KG/KM	INSTALLATION		IN-SERVICE	
							LBS	N	LBS	N
XX0021PNU	2	–	0.17	4	12	17	225	1000	65	290
XX0061PNU	6	–	0.18	5	16	24	225	1000	65	290
XX0121PNU	12	–	0.22	6	23	34	320	1423	112	500
XX0241PNU	24	–	0.32	8	45	67	320	1423	112	500

XX denotes glass type.  
 NOTE: More fiber counts are available upon request. See Fiber Optic Catalog for complete product information.  
 \*Not for aerial or direct burial applications.