

GenSPEED® 6000 Enhanced Category 6 Cable

Optimally Balanced Enhanced Performance



Features and Benefits

- Innovative cross-web design allowing for maximum pair separation, increasing key electrical performance parameters
- Performance guaranteed to 350 MHz
- TRU-Mark® print legend contains footage markings from 1000' to 0'
- Third-party verified for guaranteed performance

Applications

- IEEE 802.3: 1000 BASE-T, 100 BASE-TX, 10 BASE-T, PoE, PoE+, PoE++
- ANSI/TIA 854: 1000 BASE-TX
- CDDI, Token Ring, ATM
- Digital Video
- Broadband and Baseband Analog Video

Standard Compliances

- ANSI/TIA 568.2-D
- NEC/CEC Type CMR (UL 1666) for Non-Plenum
- NEC/CEC Type CMP (NFPA 262) for Plenum
- UL Listed CMP-LP (0.5A) for Plenum*
- UL 444
- RoHS Compliant Directive 2011/65/EU
- ANSI/TIA 862 (Building Automation)
- ICEA S-116-732
- ICEA S-102-700
- ISO/IEC 11801 Ed. 2.0 (Class E)

* 0.5A is the ampacity rating of the cable, which equates to 100 watts using 50 volts over four pairs.

Rev. Dec-2024

CONSTRUCTION

Conductors

- 23 AWG solid bare annealed copper

Separator

- Cross-web

Insulation

- Non-Plenum: Polyolefin
- Plenum: FEP, Polyolefin

Rip Cord

- Applied longitudinally under jacket

Color Code

- Pair 1: Blue-White/Blue
- Pair 2: Orange-White/Orange
- Pair 3: Green-White/Green
- Pair 4: Brown-White/Brown

Jacket

- Non-Plenum: Flame-Retardant PVC
- Plenum: Low-Smoke, Flame-Retardant PVC

PHYSICAL DATA

	CMR (Non-Plenum)	CMP (Plenum)
Nominal Cable Diameter (in)	0.240	0.230
Nominal Cable Weight (lbs/1000 ft)	28	28
Minimum Bend Radius (in)	1.0	1.0
Maximum Pulling Force (lbs)	32	32
Temperature Rating (°C)		
Installation:	0 to +60	0 to +60
Operation:	-20 to +75	-20 to +75

PART NUMBERS

Standard packaging: 1000' Spool

Jacket Color	Pull-Pac® II		Spool-Pac®		Spool	
	CMR (Non-Plenum)	CMP (Plenum)	CMR (Non-Plenum)	CMP (Plenum)	CMR (Non-Plenum)	CMP (Plenum)
Blue	7133900	7131900	7133940	7131940	7133960	7131960
	7133901	7131901	7133941	7131941	7133961	7131961
Yellow	7133902	7131902	7133942	7131942	7133962	7131962
Gray	7133903	7131903	7133943	7131943	7133963	7131963
Red	7133904	7131904	7133944	7131944	7133964	7131964
Orange	7133905	7131905	7133945	7131945	7133965	7131965
Green	7133906	7131906	7133946	7131946	7133966	7131966
Black	7133907	7131907	7133947	7131947	7133967	7131967
Pink	7133908	7131908	7133948	7131948	7133968	7131968
Purple	7133909	7131909	7133949	7131949	7133969	7131969

Note: Bulk reels are available as a special request with a maximum allowable length of 3000 feet per reel. Minimum run and lead time may apply.

Non-stock items may be subject to minimum order quantities.

GenSPEED® 6000 Enhanced Category 6 Cable

ELECTRICAL PERFORMANCE


Frequency MHz	PSACR** (min)	ACR** (min)	Insertion Loss (min)		PSNEXT (min)		NEXT (min)	
	PG Guaranteed	PG Guaranteed	TIA 568.2-D	PG Guaranteed	TIA 568.2-D	PG Guaranteed	TIA 568.2-D	PG Guaranteed
1	75.3	77.3	2.0	2.0	72.3	77.3	74.3	79.3
4	64.5	66.5	3.8	3.8	63.3	68.3	65.3	70.3
10	56.4	58.4	6.0	5.9	57.3	62.3	59.3	64.3
16	51.7	53.8	7.6	7.5	54.2	59.3	56.2	61.3
20	49.4	51.4	8.5	8.4	52.8	57.8	54.8	59.8
31.25	44.3	46.3	10.7	10.6	49.9	54.9	51.9	56.9
62.5	35.1	37.1	15.4	15.3	45.4	50.4	47.4	52.4
100	27.6	29.6	19.8	19.7	42.3	47.3	44.3	49.3
150	20.0	22.0	24.7	24.7	39.7	44.7	41.7	46.7
200	13.8	15.8	29.0	29.0	37.8	42.8	39.8	44.8
250	8.7	10.7	32.8	32.6	36.3	41.3	38.3	43.3
350	—	1.7	—	39.5	—	39.2	—	41.2
500	—	—	—	48.6	—	36.8	—	38.8

Note: Values are expressed in dB per 100 m (328 ft.) length @ 20°C. Results beyond 350 MHz for reference only.
*PSACR & ACR not specified in ANSI/TIA 568.2-D

Frequency MHz	PSACRF (min)		ACRF (min)		Return Loss (min)		TCL (min)		ELTCTL (min)	
	TIA 568.2-D	PG Guaranteed	TIA 568.2-D	PG Guaranteed	TIA 568.2-D	PG Guaranteed	TIA 568.2-D	PG Guaranteed	TIA 568.2-D	PG Guaranteed
1	64.8	69.8	67.8	72.8	20.0	21.0	40.0	40.0	35.0	35.0
4	52.8	57.7	55.7	60.7	23.0	24.0	40.0	40.0	23.0	23.0
10	44.8	49.8	47.8	52.8	25.0	26.0	40.0	40.0	15.0	15.0
16	40.7	45.7	43.7	48.7	25.0	26.0	38.0	38.0	10.9	10.9
20	38.8	43.7	41.7	46.7	25.0	26.0	37.0	37.0	9.0	9.0
31.25	34.9	39.9	37.9	42.9	23.6	24.6	35.1	35.1	—	5.1
62.5	28.9	33.8	31.8	36.8	21.5	22.5	32.0	32.0	—	5.0
100	24.8	29.8	27.8	32.8	20.1	21.1	30.0	30.0	—	5.0
150	21.3	26.3	24.3	29.3	18.9	19.9	28.2	28.2	—	5.0
200	18.8	23.8	21.8	26.8	18.0	19.0	27.0	27.0	—	5.0
250	16.8	21.8	19.8	24.8	17.3	18.3	26.0	26.0	—	5.0
350	—	18.9	—	21.9	—	17.3	—	—	—	—
500	—	15.8	—	18.8	—	16.2	—	—	—	—

Note: Values are expressed in dB per 100 m (328 ft.) length @ 20°C. Results beyond 350 MHz for reference only.

CROSS-SECTION



ELECTRICAL CHARACTERISTICS

	Max.	Nom.
DC Resistance Ohms/100 m (328 ft) @ 20°C	9.38	7.20
DC Resistance Unbalanced Individual Pair %	4.00	< 1
Delay Skew (Max) ns/100 m	45	CMP: 30 CMR: 40
Nom. Velocity of Propagation % Speed of Light		CMP: 70 CMR: 68
Characteristic Impedance Frequency (f): 1-500 MHz		Ohms 100 ± 15