

GenSPEED® 6 Category 6 Cable

Standards-Compliant



PART NUMBERS

Standard packaging: 1000' Lengths

Jacket Color		Pull-Pac® II		Spool-Pac®		Spool	
		CMR (Non-Plenum)	CMP (Plenum)	CMR (Non-Plenum)	CMP (Plenum)	CMR (Non-Plenum)	CMP (Plenum)
	Blue	7133800	7131100	7133840	7131140	7133860	7131160
	White	7133801	7131101	7133841	7131141	7133861	7131161
	Yellow	7133802	7131102	7133842	7131142	7133862	7131162
	Gray	7133803	7131103	7133843	7131143	7133863	7131163
	Red	7133804	7131104	7133844	7131144	7133864	7131164
	Orange	7133805	7131105	7133845	7131145	7133865	7131165
	Green	7133806	7131106	7133846	7131146	7133866	7131166
	Black	7133807	7131107	7133847	7131147	7133867	7131167
	Pink	7133808	7131108	7133848	7131148	7133868	7131168
	Purple	7133809	7131109	7133849	7131149	7133869	7131169

Note: Bulk reels are available as a special request with a maximum allowable length of 3000 feet per reel.

Minimum run and lead time may apply.

Non-stock items may be subject to minimum order quantities.

PHYSICAL DATA

	CMR (Non-Plenum)	CMP (Plenum)
Nominal Cable Diameter (in)	0.220	0.205
Nominal Cable Weight (lbs/1000 ft)	24	25
Minimum Bend Radius (in)	1.0	1.0
Maximum Pulling Force (lbs)	32	32
Temperature Rating (°C)		
Installation:	0 to +60	0 to +60
Operation:	-20 to +75	-20 to +75

CONSTRUCTION:

Conductors

- Non-Plenum: 23 AWG solid bare annealed copper
- Plenum: 24 AWG solid bare annealed copper

Insulation

- Non-Plenum: Polyolefin
- Plenum: FEP, Polyolefin

Color Code

- Pair 1: Blue-White/Blue
- Pair 2: Orange-White/Orange
- Pair 3: Green-White/Green
- Pair 4: Brown-White/Brown

Separator

- Divider

Rip Cord

- Applied longitudinally under jacket

Jacket

- Non-Plenum: Flame-Retardant PVC
- Plenum: Low-Smoke, Flame-Retardant PVC

Features and Benefits

- Unique separator design engineered for consistent electrical performance
- TRU-Mark® print legend contains footage markings from 1000' to 0'
- Third-party verified for guaranteed performance
- Made in U.S.A.

Applications

- IEEE 802.3: 1000 BASE-T, 100 BASE-TX, 10 BASE-T, PoE, PoE+, PoE++
- ANSI/TIA 854: 1000 BASE-TX
- CDDI, Token Ring, ATM
- Digital Video
- Broadband and Baseband Analog Video

Standard Compliances

- ANSI/TIA 568.2-E
- NEC/CEC Type CMR (UL 1666) for Non-Plenum
- NEC/CEC Type CMP (NFPA 262) for Plenum
- UL 444
- RoHS Compliant Directive 2011/65/EU
- ANSI/TIA 862 (Building Automation)
- ICEA S-116-732
- ISO/IEC 11801 Ed. 2.0 (Class E)

GenSPEED® 6 Category 6 Cable


Standards-Compliant

ELECTRICAL PERFORMANCE

Frequency MHz	PSACR* (min)	ACR* (min)	Insertion Loss (max)	PSNEXT (min)	NEXT (min)	PSACRF (min)	ACRF (min)	Return Loss (min)	TCL (min)	ELTCTL (min)
1	70.3	72.3	2.0	72.3	74.3	64.8	67.8	20.0	40.0	35.0
4	59.3	61.5	3.8	63.3	65.3	52.8	55.7	23.0	40.0	23.0
10	51.3	53.3	6.0	57.3	59.3	44.8	47.8	25.0	40.0	15.0
16	46.7	48.7	7.6	54.2	56.2	40.7	43.7	25.0	38.0	10.9
20	44.3	46.3	8.5	52.8	54.8	38.8	41.7	25.0	37.0	9.0
31.25	39.2	41.2	10.7	49.9	51.9	34.9	37.9	23.6	35.1	—
62.5	29.9	32.0	15.4	45.4	47.4	28.9	31.8	21.5	32.0	—
100	22.5	24.5	19.8	42.3	44.3	24.8	27.8	20.1	30.0	—
150	14.9	16.9	24.7	39.7	41.7	21.3	24.3	18.9	28.2	—
200	8.8	10.8	29.0	37.8	39.8	18.8	21.8	18.0	27.0	—
250	3.5	5.5	32.8	36.3	38.3	16.8	19.8	17.3	26.0	—
350	—	—	39.8	34.1	36.1	13.9	16.9	16.3	—	—
400	—	—	43.0	33.3	35.3	12.8	15.8	15.9	—	—
500	—	—	48.9	31.8	33.8	10.8	13.8	15.2	—	—

Note: Values are expressed in dB per 100 m (328 ft.) length @ 20 °C. Results beyond 250 MHz for reference only.
*PSACR & ACR not specified in ANSI/TIA 568.2-E

CROSS-SECTION



ELECTRICAL CHARACTERISTICS

	Max.
DC Resistance Ohms/100 m (328 ft) @ 20 °C	9.38
DC Resistance Unbalanced Individual Pair %	4.00
Nom. Velocity of Propagation % Speed of Light	CMP: 70 CMR: 68
Characteristic Impedance Frequency (f): 1-250 MHz	Ohms 100 ± 15