



Downhole Cables

TEC (Instrumentation and Power Cables)

SPECIALTY TEC: TEC WITH BUMPER BARS

TEC - Tubing Encased Cable (TEC) is designed and manufactured to withstand the varying harsh environments found associated with the oil and gas industry. The cable can be utilized for data transmission such as downhole gauge application through to larger cores where power is required or a combination of both.

APPLICATION

Bumper Bars can be added to any downhole cable to improve crush resistance and increase longitudinal strength.

STANDARDS & APPROVALS

Advanced Well Equipment Standard
Group AWES Recommended Practice
for Qualification of Tubing
Encapsulated Conductor
AWESTEC_01

QUALITY & TESTING

Manufactured in accordance with standard Inspection and Quality Plans
Downhole cables are manufactured according to applicable ASTM standards for each specific material:

- Alloy 825: ASTM B704 and B751
- Stainless Steel 316L: ASTM A450 and A632

The pressure ratings of TEC are based on the collapse pressure of the 1/4" tube, not burst pressures normally associated with capillary tubes. The collapse (yield) pressure is calculated using API Bulletin 5C3 Formula # 1 - Yield Strength Collapse Pressure Formula

DESIGN & CONSTRUCTION

- Temperature ranges up to 260°C
- Multiple conductor
- Outer tube is tig welded and drawn through a die to final size
- Application Specific
- Double Extruded Filler
- Custom Line Marking
- Safety-Strip® Encapsulation
- Continuous Length up to 100,000 ft

Outer Tube Materials

- 316L Stainless Steel (UNS 31603)
- A825 Alloy (UNS N08825)

Outer Tube Sizes

- 1/8" to 3/8"

Double Extruded Centralized Core

- Size : 4 AWG - 28 AWG
- Type: Solid or Stranded Conductor
- Plating (if required): Tin, Nickel, or Silver plating

Encapsulation (Optional)

- PP (Polypropylene) / TPR (Santoprene) / PA (Nylon) / PVDF / ETFE (Tefzel) / ECTFE (Halar) / FEP / PFA / ECA 3000
- Round or Square profile

Pressure Rating

- 1/8" up to 25Kpsi
- 1/4" up to 25Kpsi
- 3/8" up to 20Kpsi



CONTACT INFO:

downhole@prysmian.com
na.prysmian.com