

600 Volt USEI90

Low Voltage Utility Cables



DESCRIPTION

A twisted assembly, consisting of multiple aluminum phase conductors and one neutral conductor, each insulated with a low temperature, moisture resistant cross-linked polyethylene (XLPE) insulation that is formulated for a balance of flexibility and mechanical toughness, and a PVC jacket.

SPECIFICATIONS AND RATINGS

CSA - CSA C22.2 No. 52 -40°C / FT1 / Sunlight Resistant
For 90°C wet or dry operation.

OPTIONS

- Colored jacket
- Copper or ACM conductors
- Polyethylene-insulated USEI 75

INSTALLATION

- Conduit in Air
- Direct Buried
- Underground Duct
- Wet Locations
- Dry Locations
- Utility Secondary
- Industrial

DESIGN PARAMETERS

CONDUCTORS: Multiple, Class B Compact, aluminum alloy 1350 per ASTM.


PHASE INSULATION: High dielectric strength low temperature cross-linked polyethylene (XLPE) insulation, exhibiting an optimum balance of mechanical and electrical properties to assure extended cable life.

ASSEMBLY: Full or reduced neutral conductor, insulated and jacketed, class compact concentric strand aluminum alloy 1350 per ASTM, twisted together with the phase conductors.

JACKET: Low-temperature appropriately colored polyvinyl chloride (PVC) jacket is extruded over each individual cable.

600 Volt USEI90

Low Voltage Utility Cables



Product Number	Phase Conductors	Neutral Conductor	Insulation Thickness (mils)		Jacket Thickness (mils)		Approximate Diameter (mm)			Cable Weight (kg/km)	† Ampacity (Amps)
			Phase	Neutral	Phase	Neutral	(A)	(B)	(C)		
600 Volt Aluminum Three Conductor											
Q0RLROC	2-1/C 2/0 AWG AL	2/0 AWG AL	55	55	45	45	14.94	14.94	32.26	909	150
Q0SLQYC	2-1/C 3/0 AWG AL	1/0 AWG AL	55	55	45	45	16.15	13.92	34.90	980	175
Q0SLSOC	2-1/C 3/0 AWG AL	3/0 AWG AL	55	55	45	45	16.15	16.15	34.90	1089	175
Q0TLRYC	2-1/C 4/0 AWG AL	2/0 AWG AL	55	55	45	45	17.48	14.94	37.74	1176	205
Q0TLT0C	2-1/C 4/0 AWG AL	4/0 AWG AL	55	55	45	45	17.48	17.48	37.74	1311	205
Q0ULSYC	2-1/C 250 MCM AL	3/0 AWG AL	65	55	65	45	20.32	16.15	43.94	1488	230
Q0ULU0C	2-1/C 250 MCM AL	250 MCM AL	65	65	65	65	20.32	20.32	43.94	1687	230
Q0VLUYC	2-1/C 350 MCM AL	250 MCM AL	65	65	65	65	22.73	20.29	49.10	2028	280
Q0VLV0C	2-1/C 350 MCM AL	350 MCM AL	65	65	65	65	22.73	22.73	49.10	2199	280
Q0WLVYC	2-1/C 500 MCM AL	350 MCM AL	65	65	65	65	25.81	22.73	55.75	2695	350

PRODUCT NOTES:


† Ampacities are based on the following:

The above dimensions are approximate and subject to normal manufacturing tolerances.
All metric (SI) dimensions are derived from a soft conversion

Canadian Electrical Code, Part 1, Rule 4-004, Subrule (2)(b), as specified in Table 4, 2- or 3-conductor cable, 85-90°C conductor temperature, 30°C ambient temperature

600 Volt USEI90

Low Voltage Utility Cables



Product Number	Phase Conductors	Neutral Conductor	Insulation Thickness (mils)		Jacket Thickness (mils)		Approximate Diameter (mm)			Cable Weight (kg/km)	† Ampacity (Amps)
			Phase	Neutral	Phase	Neutral	(A)	(B)	(C)		
600 Volt Aluminum Four Conductor											
Q0MMKYC	3-1/C 2 AWG AL	4 AWG AL	45	45	30	30	10.87	9.47	23.47	578	100
Q0QMMYC	3-1/C 1/0 AWG AL	2 AWG AL	55	45	45	30	13.92	10.87	30.07	920	135
Q0TMRYC	3-1/C 4/0 AWG AL	2/0 AWG AL	55	55	45	45	17.48	14.94	37.74	1614	205
Q0TMT0C	3-1/C 4/0 AWG AL	4/0 AWG AL	55	55	45	45	17.48	17.48	37.74	1750	205

PRODUCT NOTES:

† Ampacities are based on the following:

The above dimensions are approximate and subject to normal manufacturing tolerances.
All metric (SI) dimensions are derived from a soft conversion

Canadian Electrical Code, Part 1, Rule 4-004, Subrule (2)(b), as specified in Table 4, 2- or 3-conductor cable, 85-90°C conductor temperature, 30°C ambient temperature