



MassLink™ with 200µm Fiber FlexRibbon® Technology

Ultra compact ribbon design for access or data center applications
576 to 6912 Fiber Designs



OVERVIEW

MassLink™ with FlexRibbon® Technology provides an ultracompact outside plant cable design that contains up to 6912 bend insensitive fibers. By using FlexRibbon technology, ribbons are rolled up and packed together in small diameter 144 and 288 fiber sub units. While FlexRibbon provides high packing density, these 200 µm fiber ribbons still provide the advantages of mass fusion splicing.

FEATURES AND BENEFITS

Ultra Compact Design

- FlexRibbons are rolled up into compact 144 to 288 fiber sub units for easier routing
- Significantly smaller diameter and lighter weight cables allow for easier installation and the use of smaller ducts
- These designs can be installed in smaller ducts than conventional flat ribbon which maximizes duct space utilization

FlexRibbon Technology

- Extremely flexible ribbons can be rolled up for high packing densities or laid flat for ribbon splicing
- 12 fiber ribbons are compatible with mass fusion heat strippers, cleavers, and splice machines
- Uses standard 200 µm coated bend-insensitive fiber (ITU G657.A1)

Route-able Tubes vs Compact Cable

- The RLFW1JKT 864 and 1728f designs are made with larger route-able tubes. The tubes are made larger in order to be more robust and not kink during routing
- The remaining designs are made with smaller, more condensed tubes to provide a more compact cable, so the tube can not be routed

Performance

- Uses full dry water blocking technology in the tubes and cable core for easy closure preparation and termination
- Tested in accordance with GR 20/ICEA 640 and with relevant EIA/TIA-455 series FOTPs for fiber optic cables

Registered Supplier

- ISO 9001, ISO 14001, TL 9000, and OHSAS 18001

PERFORMANCE SPECIFICATIONS

Tensile Rating	N	lbf		
Installation	2700	600		
Residual	800	180		
Crush Resistance	N/cm	lbf/in		
Short/ Long Term	220/110	125/63		
Temperature Ratings	°C		°F	
	Route-able	Non Route-able	Route-able	Non Route-able
Operation	-30 to +70	-20 to +70	-22 to +158	-4 to +158
Installation	-20 to +60		-4 to +140	
Storage/Shipping	-40 to +70		-40 to +158	

CABLE BENDING - NON-ROUTE-ABLE TUBE DESIGNS

Fiber Count	576-864	1152-1728	3456	6912
Minimum Bend Diameter (Diameter = Radius x 2)				
Installation: Wheel/Capstan	27 in (68 cm)	34 in (85 cm)	49 in (124 cm)	50 in (127 cm)
Long Term: Coil/Slack/Bend	14 in (36 cm)	18 in (45 cm)	26 in (65 cm)	32 in (82 cm)
Minimum Bend Radius (Diameter = Radius x 2)				
Installation: Wheel/Capstan	20 x Cable OD			16 x Cable OD
Long Term: Coil/Slack/Bend	10 x Cable OD			
Duct Size / % Fill	1" / 67%	1" / 84%	1½" / 81%	2" / 77%

CABLE BENDING - ROUTE-ABLE TUBE DESIGNS

Fiber Count	576-864	1152-1728
Minimum Bend Diameter (Diameter = Radius x 2)		
Installation: Wheel/Capstan	31 in (78 cm)	39 in (100 cm)
Long Term: Coil/Slack/Bend	16 in (41 cm)	21 in (52 cm)
Minimum Bend Radius (Diameter = Radius x 2)		
Installation: Wheel/Capstan	20 x Cable OD	
Long Term: Coil/Slack/Bend	10 x Cable OD	
Duct Size / % Fill	1" / 77%	1.25" / 78%



Prysmian

4 Tesseneer Drive, Highland Heights, KY 41076
na.prysmian.com
TLS-DS-A-310-0525

MassLink™ with 200µm Fiber FlexRibbon® Technology

Ultra compact ribbon design for access or data center applications
576 to 6912 Fiber Designs



RIBBON COLOR CODE			
Ribbon #	Marking	Ribbon #	Marking
1		13	■ ■ ■
2		14	■ ■ ■
3		15	■ ■ ■ ■
4		16	■ ■ ■ ■
5	■	17	■ ■ ■ ■
6	■	18	■ ■ ■ ■
7	■	19	■ ■ ■ ■
8	■	20	■ ■ ■ ■ ■
9	■	21	■ ■ ■ ■ ■
10	■ ■	22	■ ■ ■ ■ ■
11	■ ■	23	■ ■ ■ ■ ■
12	■ ■	24	■ ■ ■ ■ ■

Fiber Count Range	Recommended Fiber Count	Recommended Prysmian* Part Number	# of Tubes	# of Ribbons/ Tube	# of Fibers/ Tube	Buffer Tube OD		Cable OD		Approx. Cable Weight		Max. Reel Length	
						Inches	mm	Inches	mm	lb/kft	kg/km	feet	meters

Non-Route-able Tube Design

576-864	864	RLF1JKT-12-AA-864-BB	6	12	144	0.19	4.7	0.67	17.0	134	199	33,792	10,300
1152-1728	1728	RLF1JKT-12-AA-1728-BB	6	24	288	0.24	6.2	0.84	21.3	211	313	21,653	6,600
3456	3456	RL2F1JKT-12-AA-3456-BB	24	12	144	0.18	4.5	1.22	30.9	422	628	11,631	3,545
6912	6912	RLF1JKT-12-AA-6912-BB	24	24	288	0.24	6.2	1.53	38.9	634	943	10,050	3,063

Route-able Tube Design

576-864	864	RLFW1JKT-12-AA-864-BB	6	12	144	0.22	5.5	0.77	19.5	164	245	31,824	9,700
1152-1728	1728	RLFW1JKT-12-AA-1728-BB	6	24	288	0.28	7.2	0.98	24.9	249	370	19,685	6,000

* Where AA equals glass type and BB equals attenuation



MassLink™ with 200µm Fiber FlexRibbon® Technology

Ultra compact ribbon design for access or data center applications
576 to 6912 Fiber Designs



Ordering Guide

The Prysmian part number incorporates several significant attributes involving cable design and optical performance. The appropriate part number can be configured using the process described below

Example: 6912 count all-dielectric MassLink with FlexRibbon Technology with G657.A2 bend insensitive fiber. (printed in feet)

1	LENGTH MARKINGS	2	PRODUCT FAMILY	3	CONSTRUCTION	4	FIBER GROUPING	5	FIBER TYPE	6	FIBER COUNT	7	FIBER GRADE
	F	–	RLF		1JKT	–	12	–	22	–	6912	–	EA

PART NUMBER CONSTRUCTION	
1	LENGTH MARKINGS
F = Feet, M = Meters, or B = BABA Compliant in Feet	
2	PRODUCT FAMILY
RLF = MassLink with FlexRibbon Technology (576-1728 & 6912 Non-Route-able Tubes)	
RL2F = MassLink with FlexRibbon Technology (3456 Non-Route-able Tubes)	
RLFW = MassLink with FlexRibbon Technology (576-1728 Route-able Tubes)	
3	CONSTRUCTION
1JKT = Single Jacket	
4	FIBER GROUPING
12 = 12f per ribbon	

FIBER INFORMATION		
5	FIBER TYPE	
SINGLE-MODE		
2X = BBXS™ Bend Insensitive 200 μm Single- Mode (ITU G.657.A2 & G.652.D)		
22 = 200 μm Bend Insensitive Single-Mode (ITU G.657.A2 & G.652.D)		
6	FIBER COUNT	
576 to 6912 fibers		
7	FIBER GRADE	
SINGLE-MODE		
Attenuation (dB/km)	Wavelength (nm)	Fiber Type
Fiber Counts 576-864, 1152-1728, 3456 & 6912 EA = 0.5/0.5/0.5	1310/1383/1550	2X, 22
Fiber Counts 576-864 & 1152-1728 E7 = 0.4/0.4/0.3	1310/1383/1550	2X, 22

Notes: Please refer to the Fiber Code Addendum for additional fiber options, or contact us for help.
Other cable constructions and fiber performance grades available on request.

