



288 to 432F FusionLink™ RICT Indoor/Outdoor Riser with FlexRibbon™ 200 μm Fibers




Strength Member
Ripcord
Dry Water-Blocked Buffer Tube
Ribbons
Water Blocking Tape
Outer Jacket



Indoor/Outdoor Design



Strength Member
Ripcord
Dry Water-Blocked Buffer Tube
Ribbons
Water Blocking Tape
Outer Jacket



Indoor Design

OVERVIEW

FusionLink™ RICT with FlexRibbon™ Technology provides an ultracompact indoor/outdoor cable design that contains up to 432 bend insensitive fibers. By using FlexRibbon technology, ribbons are rolled up and packed together in a small diameter central tube. While FlexRibbon™ provides high packing density, these 200 μm fiber ribbons still provide the advantages of mass fusion splicing.

FEATURES AND BENEFITS

Ultra Compact Design

- FlexRibbons™ are rolled up into compact central tube designs
- Significantly smaller diameter and lighter weight cables allow for easier installation and the use of smaller ducts

FlexRibbon Technology

- Extremely flexible ribbons can be rolled up for high packing densities or laid flat for ribbon splicing
- 12 fiber ribbons are compatible with mass fusion heat strippers, cleavers, and splice machines
- Uses standard 200 μm coated bend-insensitive fiber (ITU G657.A1)

Performance

- Uses full dry water blocking technology in the tube and cable core for easy closure preparation and termination
- Tested in accordance with ICEA 696 and with relevant EIA/TIA-455 series FOTPs for fiber optic cables

Flame Retardant Construction

- Riser designs comply with UL 1666 and is OFNR and OFNG-FT4 rated

Registered Supplier

- ISO 9001, ISO 14001, TL 9000, and OHSAS 18001

PERFORMANCE SPECIFICATIONS		
Fiber Count	288 to 432	
Tensile Rating	N	lbf
Installation	2,700	600
Residual	800	180
Crush Resistance	N/cm	lbf/in
Short/ long Term	220/80	
Temperature Ratings	°C	°F
Operation	-30 to +70	-22 to +158
Installation	-10 to +60	+14 to +140
Storage/Shipping	-40 to +70	-40 to +158
Duct Size/% Fill	1" / 62%	



Prysmian

4 Tessenere Drive, Highland Heights, KY 41076
na.prysmian.com
TLS-DS-B-207-0624

288 to 432F FusionLink™ RICT Indoor/Outdoor Riser with FlexRibbon™ 200 μm Fibers



RIBBON COLOR CODE					
Ribbon #	Marking	Ribbon #	Marking	Ribbon #	Marking
1		13		25	
2		14		26	
3		15		27	
4		16		28	
5		17		29	
6		18		30	
7		19		31	
8		20		32	
9		21		33	
10		22		34	
11		23		35	
12		24		36	

CABLE BENDING	
Fiber Count	288 to 432
Minimum Bend Diameter (Diameter = Radius x 2)	
Installation: Wheel/Capstan	25in (63cm)
Long Term: Coil/Slack/Bend	13in (33cm)
Minimum Bend Radius (Diameter = Radius x 2)	
Installation: Wheel/Capstan	20 x Cable OD
Long Term: Coil/Slack/Bend	10 x Cable OD

Fiber Count	Recommended Prysmian** Part Number	Number of Ribbons	Fibers per Tube	Buffer Tube OD		Cable OD		Approx. Cable Weight		Max. Reel Length	
				Inches	mm	Inches	mm	lb/kft	kg/km	feet	meters

INDOOR/OUTDOOR

FusionLink™ Indoor/Outdoor with FlexRibbon™ | OFNR/FT4

288	RRIOCFK-12-AA-288-BB	24	288	0.35	8.8	0.62	15.8	147	218.6	40354	12,300
432	RRIOCFK-12-AA-432-BB	36	432	0.35	8.8	0.62	15.8	153	227	40354	12,300

INDOOR ONLY

FusionLink™ Indoor Only with FlexRibbon™ | OFNR/FT4

288	RRCFK-12-AA-288-BB	24	288	0.35	8.8	0.62	15.8	147	218.6	40354	12,300
432	RRCFK-12-AA-432-BB	36	432	0.35	8.8	0.62	15.8	153	227	40354	12,300

**Where AA equals glass type and BB equals attenuation code

Ordering Guide

The Prysmian Group part number incorporates several significant attributes involving cable design and optical performance. The appropriate part number can be configured using the process described below

Example: 432 count all-dielectric FusionLink RICT with FlexRibbon Technology with G657.A2 bend insensitive fiber (printed in feet)

1	LENGTH MARKINGS	2	PRODUCT FAMILY	3	CONSTRUCTION	4	FIBER GROUPING	5	FIBER TYPE	6	FIBER GRADE
	F		RRIOCFK		12		2X		432		EA

PART NUMBER CONSTRUCTION	
1	LENGTH MARKINGS
F = Feet or M = Meters	
2	PRODUCT FAMILY & CONSTRUCTION
RRIOCFK = FusionLink Indoor/Outdoor Riser FlexRibbon (Black Jacket)	
RRCFK = FusionLink Indoor Only Riser FlexRibbon (Yellow Jacket)	
3	FIBER GROUPING
12 = 12f per tube	

FIBER INFORMATION	
4	FIBER TYPE
SINGLE-MODE	
2X = BBXS 200um Bend Insensitive Single-Mode (ITU G.657.A2 & G652.D)	
5	FIBER COUNT
288 to 432 fibers	
6	FIBER GRADE
EA = 0.5/0.5/0.5 db/km @ 1310/1383/1550 nm	
E7 = 0.4/0.4/0.3 db/km @ 1310/1383/1550 nm	

Note: Please refer to the Fiber Code Addendum for additional fiber options, or contact us for help. Other cable constructions and fiber performance grades available on request.



Prysmian

4 Tesseneer Drive, Highland Heights, KY 41076
na.prysmian.com
TLS-DS-B-207-0624