




# 288 MicroFlex™ RICT Indoor/Outdoor Riser with FlexRibbon® 200µm fibers, for use in microducts




- Ripcord
- Strength Yarns
- Dry Water-Blocked Buffer Tube
- Ribbons
- Water Blocking Tape
- Outer Jacket



Indoor/Outdoor



- Ripcord
- Strength Yarns
- Dry Water-Blocked Buffer Tube
- Ribbons
- Water Blocking Tape
- Outer Jacket



Indoor Only

## OVERVIEW

MicroFlex RICT with FlexRibbon® Technology provides an ultracompact indoor/outdoor cable design that contains up to 288 bend insensitive fibers. By using FlexRibbon technology, ribbons are rolled up and packed together in a small diameter MicroFlex central tube. While FlexRibbon provides high packing density, these 200µm fiber ribbons still provide the advantages of mass fusion splicing.

## FEATURES AND BENEFITS

### Ultra Compact MicroFlex Design

- FlexRibbons are rolled up into compact central tube designs
- Significantly smaller diameter and lighter weight cables allow for easier installation and the use of smaller ducts

### FlexRibbon Technology

- Extremely flexible ribbons can be rolled up for high packing densities or laid flat for ribbon splicing
- 12 fiber ribbons are compatible with mass fusion heat strippers, cleavers, and splice machines
- Uses standard 200 µm coated bend-insensitive fiber (ITU G657.A2)

### Performance

- Uses full dry water blocking technology in the tube and cable core for easy closure preparation and termination
- Tested in accordance with ICEA 696 and with relevant EIA/TIA-455 series FOTPs for fiber optic cables

### Flame Retardant Construction

- Riser designs comply with UL 1666 and is OFNR and OFNG-FT4 rated

### Registered Supplier

- ISO 9001, ISO 14001, TL 9000, and OHSAS 18001

PERFORMANCE SPECIFICATIONS		
Fiber Count	288	
<b>Tensile Rating</b>	<b>N</b>	<b>lbf</b>
<b>Installation</b>	2,700	600
<b>Residual</b>	800	180
<b>Crush Resistance</b>	<b>N/cm</b>	<b>lbf/in</b>
<b>Short/ long Term</b>	220/110	125/63
<b>Temperature Ratings</b>	<b>°C</b>	<b>°F</b>
<b>Operation</b>	-20 to +70	-4 to +158
<b>Installation</b>	-10 to +60	+14 to +140
<b>Storage/Shipping</b>	-40 to +70	-40 to +158
<b>Duct Size/% Fill</b>	13mm / 77%	



### Prysmian

4 Tessenere Drive, Highland Heights, KY 41076  
na.prysmian.com  
TLS-DS-B-208-0426

# 288 MicroFlex™ RICT Indoor/Outdoor Riser with FlexRibbon® 200µm fibers , for use in microducts



RIBBON COLOR CODE			
Ribbon #	Marking	Ribbon #	Marking
1		13	■ ■ ■
2		14	■ ■ ■
3		15	■ ■ ■
4		16	■ ■ ■ ■
5	■	17	■ ■ ■ ■
6	■	18	■ ■ ■ ■
7	■	19	■ ■ ■ ■
8	■	20	■ ■ ■ ■
9	■	21	■ ■ ■ ■
10	■ ■	22	■ ■ ■ ■
11	■ ■	23	■ ■ ■ ■
12	■ ■	24	■ ■ ■ ■

CABLE BENDING	
Fiber Count	288
Minimum Bend Diameter (Diameter = Radius x 2)	
Installation: Wheel/Capstan	16in (40cm)
Long Term: Coil/Slack/Bend	8in (21cm)
Minimum Bend Radius (Diameter = Radius x 2)	
Installation: Wheel/Capstan	20 x Cable OD
Long Term: Coil/Slack/Bend	10 x Cable OD

Fiber Count	Recommended Prysmian** Part Number	Number of Ribbons	Fibers per Tube	Buffer Tube OD		Cable OD		Approx. Cable Weight		Max. Reel Length	
				Inches	mm	Inches	mm	lb/kft	kg/km	feet	meters

### INDOOR/OUTDOOR OFNR/FT4

288	RRIOCFKMD-12-AA-288-BB	24	288	0.25	6.4	0.40	10.1	75	112	15,000	4,572
-----	------------------------	----	-----	------	-----	------	------	----	-----	--------	-------

### INDOOR ONLY OFNR/FT4

288	RRCFKMD-12-AA-288-BB	24	288	0.25	6.4	0.40	10.1	75	112	15,000	4,572
-----	----------------------	----	-----	------	-----	------	------	----	-----	--------	-------

\*\*Where AA equals glass type and BB equals attenuation code

## Ordering Guide

The Prysmian part number incorporates several significant attributes involving cable design and optical performance. The appropriate part number can be configured using the process described below

**Example:** MicroFlex RICT with FlexRibbon Technology with G657.A2 bend insensitive fiber (printed in feet)

1	LENGTH MARKINGS	2	PRODUCT FAMILY	3	FIBER GROUPING	4	FIBER TYPE	5	FIBER COUNT	6	FIBER GRADE
	F		RRIOCFKMD		12		2X		288		EA

PART NUMBER CONSTRUCTION	
<b>1</b>	<b>LENGTH MARKINGS</b> F = Feet, M = Meters or C = Custom Print
<b>2</b>	<b>PRODUCT FAMILY &amp; CONSTRUCTION</b> RRIOCFKMD = Indoor/Outdoor Riser FlexRibbon (Black Jacket) RRCFKMD = Indoor Only Riser FlexRibbon (Yellow Jacket)
<b>3</b>	<b>FIBER GROUPING</b> 12 = 12f per tube

Note: Please refer to the Fiber Code Addendum for additional fiber options, or contact us for help.  
Other cable constructions and fiber performance grades available on request.

FIBER INFORMATION		
<b>4</b>	<b>FIBER TYPE</b>	
	SINGLE-MODE 2X = BBXS200 Bend Insensitive 200µm Single-Mode (ITU G.657.A2 & G.652.D)	
<b>5</b>	<b>FIBER COUNT</b> 288 fibers	
<b>6</b>	<b>FIBER GRADE</b>	
	SINGLE-MODE	
	Attenuation (dB/km)	Wavelength (nm) Fiber Type
	EA = 0.5/0.5/0.5	1310/1385/1550 2X



### Prysmian

4 Tessenner Drive, Highland Heights, KY 41076  
na.prysmian.com  
TLS-DS-B-208-0426