



GenSPEED® Distribution Indoor-Outdoor Tight Buffered

Riser and plenum rated cables


Prysmian



Flame Retardant Jacket
Water Blocking Strength Members
Optical Fibers



Flame Retardant Outer Jacket
Interlock Armor
Optical Fibers
Water Blocking Strength Members
Flame Retardant Inner Jacket



OVERVIEW

Prysmian's GenSPEED Distribution cable family packages up to 144 color-coded 900 µm tight buffered fibers into a single flame retardant cable. This cable design is available in both riser rated and plenum rated versions for deployment in any inside plant fire-code application. The UV-resistant outer jacket, coupled with dry waterblocking technology, address environmental concerns for outdoor use. The tight buffered distribution cable supports standard installation practices and may be easily terminated using established field connectorization methods.

SPECIFICATIONS / RATINGS

- Applications** Versatile indoor-outdoor tight buffered cable for use with field installable connectors
- Constructions** Single-Unit ($\leq 24f$); Subunits ($\geq 18f$); interlock armor optional
- Flame Ratings** Riser rated design complies with UL1666 & UL1685/IEEE1202; OFNR and OFNG-FT4 rated. Plenum rated design complies with NFPA 262; OFNP/FT6 rated
- Fiber Count** 2 to 144 (Riser), 2 to 96 (Plenum)
- Fiber Types** Single-mode (ESMF, bend-insensitive)
Multimode (62.5/125-OM1, 50/125-OM2+, OM3 & OM4)
- Standards** TIA/EIA-568, ANSI/ICEA S-83-596, ANSI/ICEA S-104-696, UL-1666, NFPA 262, CSA 22.2 Telcordia GR-409, Telcordia GR-20, CE RoHS Compliant
- Single Unit Designs – Weatherized Indoor as defined in ICEA 696 (appendix)
 - Multi Unit Designs – Indoor/Outdoor as defined in ICEA 696
- Registered Supplier** ISO 9001, ISO 14001, TL 9000, and OHSAS 18001

FEATURES AND BENEFITS

- 900 µm tight buffered fibers designed to support rapid field termination
- Industry standard color coding for quick, error-free fiber identification
- Single-Unit designs provide space savings and cost advantages
- Subunit construction improves organization and termination practices
- Available with bend-insensitive single-mode and multimode optical fibers
- Flexible, flame-retardant and UV-stable outer jacket
- Optional Interlock Armor provides robust protection and supports one-step installation
- Supports all high performance networks including OM4/10 Gigabit Ethernet systems



Prysmian

A Brand of Prysmian Group

Prysmian Group

4 Tesseneer Drive, Highland Heights, KY 41076
+1-859-572-8000 / na.prysmiangroup.com
TLS-DS-B-401-1023

GenSPEED® Distribution Indoor-Outdoor Tight Buffered

Riser and plenum rated cables



GenSPEED Distribution Indoor/Outdoor Riser C1181 Series OFNR/FT4

Fiber Count Range	Recommended Fiber Count	Recommended Part Number		Fibers per Unit	Diameter		Cable Weight		Bend Radius UNDER LOAD		Bend Radius NO LOAD		Max Installation LOAD (pull strength)		Max Operation LOAD	
		Prysmian*	General Cable**		inches	mm	lb/kft	kg/km	inches	cm	inches	cm	lbs	newtons	lbs	newtons
2	2	C1181-00-AA-002-BB	XX0021ANR	single-unit	0.19	4.8	15	22	3.8	9.6	1.9	4.8	150	660	45	200
4	4	C1181-00-AA-004-BB	XX0041ANR	single-unit	0.22	5.6	19	28	4.4	11.2	2.2	5.4	150	660	45	200
6	6	C1181-00-AA-006-BB	XX0061ANR	single-unit	0.24	6.0	21	31	4.8	12.0	2.4	5.4	150	660	45	200
8	8	C1181-00-AA-008-BB	XX0081ANR	single-unit	0.25	6.2	23	34	5.0	12.4	2.5	5.4	150	660	45	200
12	12	C1181-00-AA-012-BB	XX0121ANR	single-unit	0.28	7.0	30	45	5.6	14.0	2.8	6.2	150	660	45	200
18	18	C1181-00-AA-018-BB	XX0181ANR	single-unit	0.31	7.7	36	53	6.2	15.4	3.1	7.8	300	1330	90	400
24	24	C1181-00-AA-024-BB	XX0241ANR	single-unit	0.32	8.1	43	64	6.4	16.2	3.2	8.1	300	1330	90	400
18-24	24	C1181-06-AA-024-BB	XX0241A1R	6	0.53	13.5	103	153	10.6	27.0	5.3	14.1	600	2670	180	800
36-48	48	C1181-12-AA-048-BB	XX0481A1R	12	0.61	15.5	140	209	12.2	31.0	6.1	15.5	600	2670	180	800
72	72	C1181-12-AA-072-BB	XX0721A1R	12	0.80	20.3	208	309	16.0	40.6	8.0	20.3	600	2670	180	800
96	96	C1181-12-AA-096-BB	XX0961A1R	12	0.95	24.2	296	441	19.0	48.4	9.5	24.2	600	2670	180	800
144	144	C1181-12-AA-144-BB	XX1441A1R	12	1.02	25.9	347	516	20.4	51.8	10.2	25.9	600	2670	180	800

GenSPEED Distribution Indoor/Outdoor Plenum C1182 Series OFNP/FT6

Fiber Count Range	Recommended Fiber Count	Recommended Part Number		Fibers per Unit	Diameter		Cable Weight		Bend Radius UNDER LOAD		Bend Radius NO LOAD		Max Installation LOAD (pull strength)		Max Operation LOAD	
		Prysmian*	General Cable**		inches	mm	lb/kft	kg/km	inches	cm	inches	cm	lbs	newtons	lbs	newtons
2-4	2	C1182-00-AA-002-BB	XX0021ANU	single-unit	0.18	4.6	14	21	3.6	9.2	1.8	4.6	100	440	30	150
6	6	C1182-00-AA-006-BB	XX0061ANU	single-unit	0.20	5	15	22	4.0	10.0	2.0	5.0	100	440	30	150
8	8	C1182-00-AA-008-BB	XX0081ANU	single-unit	0.21	5.2	18	27	4.2	10.4	2.1	5.2	100	440	30	150
12	12	C1182-00-AA-012-BB	XX0121ANU	single-unit	0.24	6.1	22	33	4.8	12.2	2.4	6.1	100	440	30	150
18	18	C1182-00-AA-018-BB	XX0181ANU	single-unit	0.26	6.5	32	48	5.2	13.0	2.6	6.5	150	660	45	200
24	24	C1182-00-AA-024-BB	XX0241ANU	single-unit	0.30	7.6	42	62	6.0	15.2	3.0	7.6	150	660	45	200
18-24	24	C1182-06-AA-024-BB	XX0241A1D	6	0.46	11.6	85	126	9.2	23.2	4.6	11.6	600	2670	180	800
36-48	48	C1182-12-AA-048-BB	XX0481A1D	12	0.56	14.1	130	194	11.2	28.2	5.6	14.1	600	2670	180	800
72	72	C1182-12-AA-072-BB	XX0721A1D	12	0.74	18.7	233	347	14.8	37.4	7.4	18.7	600	2670	180	800
96	96	C1182-12-AA-096-BB	XX0961A1D	12	0.89	22.6	330	491	17.8	45.2	8.9	22.6	600	2670	180	800

*Where AA equals glass type and BB equals attenuation code

**Where XX equals glass type

Note: Cable damage may occur if installation temperature limits are exceeded; therefore, Prysmian Group recommends storing I/O cables in appropriate temperature conditions ≥ 24 hours prior to placement.

Temperature Range

Shipping and Storage:	Riser	-40° F to +158° F	(-40° C to +70° C)
	Plenum	-40° F to +158° F	(-40° C to +70° C)
Installation:	Riser	+14° F to +140° F	(-10° C to +60° C)
	Plenum	+32° F to +140° F	(0° C to +60° C)
Operation:	Riser	-40° F to +158° F	(-40° C to +70° C)
	Plenum	-40° F to +158° F	(-40° C to +70° C)

GenSPEED Distribution Indoor/Outdoor Riser with Interlock Armor C1181AJ Series OFCR/FT4

Fiber Count Range	Recommended Fiber Count	Recommended Part Number		Fibers per Unit	Diameter		Cable Weight		Bend Radius UNDER LOAD		Bend Radius NO LOAD		Max Installation LOAD (pull strength)		Max Operation LOAD	
		Prysmian*	General Cable**		inches	mm	lb/kft	kg/km	inches	cm	inches	cm	lbs	newtons	lbs	newtons
2	2	C1181AJ-00-AA-002-BB	XX0021ANR ILRA	single-unit	0.52	13.1	120	179	10.4	26.2	5.2	13.1	150	660	45	200
4-6	6	C1181AJ-00-AA-006-BB	XX0061ANR ILRA	single-unit	0.56	14.2	132	196	11.2	28.4	5.6	5.4	150	660	45	200
8	8	C1181AJ-00-AA-008-BB	XX0081ANR ILRA	single-unit	0.57	14.5	135	201	11.4	29.0	5.7	5.4	150	660	45	200
12	12	C1181AJ-00-AA-012-BB	XX0121ANR ILRA	single-unit	0.59	14.9	138	205	11.8	29.8	5.9	6.2	150	660	45	200
18	18	C1181AJ-00-AA-018-BB	XX0181ANR ILRA	single-unit	0.62	15.6	149	222	12.4	31.2	6.2	7.8	300	1330	90	400
24	24	C1181AJ-00-AA-024-BB	XX0241ANR ILRA	single-unit	0.63	16.0	161	240	12.6	32.0	6.3	8.1	300	1330	90	400
18-24	24	C1181AJ-06-AA-024-BB	XX0241A1R ILRAS	6	0.88	22.4	296	440	17.6	44.7	8.8	14.1	600	2670	180	800
36-48	48	C1181AJ-12-AA-048-BB	XX0481A1R ILRAS	12	0.97	24.6	396	589	19.4	49.2	9.7	24.6	600	2670	180	800
72	72	C1181AJ-12-AA-072-BB	XX0721A1R ILRAS	12	1.16	29.5	504	750	23.2	59.0	11.6	29.5	600	2670	180	800
96	96	C1181AJ-12-AA-096-BB	XX0961A1R ILRAS	12	1.32	33.5	603	897	26.4	67.0	13.2	33.5	600	2670	180	800
144	144	C1181AJ-12-AA-144-BB	XX1441A1R ILRAS	12	1.38	35.1	712	1060	27.6	70.2	13.8	35.1	600	2670	180	800

GenSPEED Distribution Indoor/Outdoor Plenum with Interlock Armor C1182AJ Series OFCP/FT6

Fiber Count Range	Recommended Fiber Count	Recommended Part Number		Fibers per Unit	Diameter		Cable Weight		Bend Radius UNDER LOAD		Bend Radius NO LOAD		Max Installation LOAD (pull strength)		Max Operation LOAD	
		Prysmian*	General Cable**		inches	mm	lb/kft	kg/km	inches	cm	inches	cm	lbs	newtons	lbs	newtons
2-6	2	C1182AJ-00-AA-002-BB	XX0021ANU ILPA	single-unit	0.47	12.0	90	134	9.4	24.0	4.7	12.0	100	440	30	150
8	8	C1182AJ-00-AA-008-BB	XX0081ANU ILPA	single-unit	0.49	12.3	95	141	9.8	24.6	4.9	12.3	100	440	30	150
12	12	C1182AJ-00-AA-012-BB	XX0121ANU ILPA	single-unit	0.52	13.2	99	148	10.4	26.4	5.2	13.2	100	440	30	150
18	18	C1182AJ-00-AA-018-BB	XX0181ANU ILPA	single-unit	0.54	13.6	114	170	10.8	27.2	5.4	13.6	150	660	45	200
24	24	C1182AJ-00-AA-024-BB	XX0241ANU ILPA	single-unit	0.58	14.7	131	195	11.6	29.4	5.8	14.7	150	660	45	200
18-24	24	C1182AJ-06-AA-024-BB	XX0241A1D ILPAS	6	0.73	18.5	187	279	14.6	37.0	7.3	18.5	600	2670	180	800
36-48	48	C1182AJ-12-AA-048-BB	XX0481A1D ILPAS	12	0.86	21.8	314	468	17.2	43.6	8.6	21.8	600	2670	180	800
72	72	C1182AJ-12-AA-072-BB	XX0721A1D ILPAS	12	1.05	26.7	463	689	21.0	53.4	10.5	26.7	600	2670	180	800
96	96	C1182AJ-12-AA-096-BB	XX0961A1D ILPAS	12	1.19	30.2	600	893	23.8	60.4	11.9	30.2	600	2670	180	800

*Where AA equals glass type and BB equals attenuation code

**Where XX equals glass type

Note: Cable damage may occur if installation temperature limits are exceeded; therefore, Prysmian Group recommends storing I/O cables in appropriate temperature conditions ≥ 24 hours prior to placement.


Temperature Range

Shipping and Storage:	Riser	-40° F to +158° F	(-40° C to +70° C)
	Plenum	-40° F to +158° F	(-40° C to +70° C)
Installation:	Riser	+14° F to +140° F	(-10° C to +60° C)
	Plenum	+32° F to +140° F	(0° C to +60° C)
Operation:	Riser	-40° F to +158° F	(-40° C to +70° C)
	Plenum	-40° F to +158° F	(-40° C to +70° C)

Ordering Guide

The Prysmian Group part number incorporates several significant attributes involving cable design and optical performance. The appropriate part number can be configured using the process described below

Example: GenSPEED Distribution Tight Buffered | Indoor-Outdoor Riser (OFNR/FT4), 12 fiber subunits | 48 62.5/125 Multimode Fibers total (printed in feet)



PART NUMBER CONSTRUCTION	
1	LENGTH MARKINGS
F = Feet or M = Meters	
2	PRODUCT FAMILY
Riser-FT4 C1181 = GenSPEED Distribution Indoor/Outdoor Riser Tight Buffer Flame Rating: OFNR/FT4 Fiber Count 2 to 144	
Plenum-FT6 C1182 = GenSPEED Distribution Indoor/Outdoor Plenum Tight Buffer Flame Rating: OFNP/FT6 Fiber Count 2 to 96	
3	CONSTRUCTION
(BLANK) = None	
AJ = Jacketed aluminum OFCR FT4 or OFCP FT6	
SJ = Jacketed steel OFCR FT4 or OFCP FT6	
4	FIBER GROUPING
00 = Single unit	
06 = 6f per subunit	
12 = 12f per subunit	

Note: Please refer to the Fiber Code Addendum for additional fiber options, or contact us for help.

FIBER INFORMATION				
5	FIBER TYPE			
SINGLE-MODE				
HB = Single-Mode (ITU G.652 C & D) Low Water Peak				
B1 = Bend-Insensitive Single-Mode (ITU G.657.A1 & G.652.D)				
B2 = Bend-Insensitive Single-Mode (ITU G.657.A2 & .B2, & G.652.D)				
MULTIMODE				
	Wavelength (nm)	Bandwidth (MHz)	1 GbE Dist (m)	10 GbE Dist (m)
G6 = OM1 (62.5µm)	850/1300	200/500	300/550	33/___
G5 = OM2+ BIF (50µm)	850/1300	700/500	800	150/___
G3 = OM3 BIF (50µm)	850/1300	1500/500	1000	300/___
G4 = OM4 BIF (50µm)	850/1300	3500/500	1100	550/___
6	FIBER COUNT			
2 to 144 fibers				
7	FIBER GRADE			
SINGLE-MODE				
	Attenuation (dB/km)	Wavelength (nm)	Fiber Type	
EB = 0.7/0.7/0.7		1310/1383/1550	Single-Mode	
EA = 0.5/0.5/0.5		1310/1383/1550	Bend Insensitive Single-Mode	
E7 = 0.4/0.4/0.3		1310/1383/1550	Bend Insensitive Single-Mode	
MULTIMODE				
	Attenuation (dB/km)	Wavelength (nm)	Fiber Type	
M2 = 3.5/1.0		850/1300	OM1 (62.5µm)	
M3 = 3.0/1.0		850/1300	OM2+, OM3, OM4 (50µm)	

Other cable constructions and fiber performance grades available on request.