



GenSPEED® COLink Indoor RICT Ribbon


12-864f Riser and 12-144f Plenum RICT Cable




12-432f Dielectric & Armored Riser




Plenum



864f Armored Riser



864f Dielectric Riser



FEATURES AND BENEFITS

Indoor Design

- Saves space and time by eliminating splices at the cable vault
- Can be installed using typical loose tube cable methods and hardware

Compact Design

- Efficient packaging of higher fiber counts
- Lightweight and easy to handle during installation

Easily Removable Ribbon Matrix

- Allows for ease of stripping and fiber breakout
- Improves mid-span strippability

Precision Ribbon Geometry

- Time and labor savings during fiber splicing
- Superior fiber alignment produces low skew and ease of connectorization

Flexible Buffer Tube

- Superior kink resistance
- Eliminates need for closure transportation tubing
- Facilitates route management in closures

Dry Water-Blocking Technology

- Buffer tube and core are completely dry – no gel
- Permits rapid cable preparation and termination
- Riser - Water-blocking materials are easily removed
- Plenum - No water-blocking materials used

UL and c(UL) Listed

- OFNR/FT4 for dielectric riser applications
- OFCR/FT4 for armored riser applications
- OFNP/FT6 for dielectric plenum applications

RoHS
COMPLIANT

Performance - RISER

- Meets or exceeds the requirements of Telcordia GR-20 & ICEA 640, TIA-598C, ANSI/EIA/TIA 568.3, CE RoHS Compliant and is tested in accordance with relevant EIA/TIA-455 series FOTPs for fiber optic cables
- RDUP listed (tested in accordance with PE-90)
- The complete cable and all subcomponents are RoHS-compliant

Performance - PLENUM

- Telcordia GR-409, ANSI/ICEA S-83-596, TIA-598C, ANSI/EIA/TIA 568.3, CE RoHS Compliant
- The complete cable and all subcomponents are RoHS-compliant

Registered Supplier

- ISO 9001, ISO 14001, TL 9000, and OHSAS 18001

PERFORMANCE SPECIFICATIONS

Bend Radius	RISER		PLENUM	
Dynamic	20 x Cable OD		20 x Cable OD	
Static	10 x Cable OD		10 x Cable OD	
Tensile Rating	N	lbf	N	lbf
Installation	2,700	600	660	148
Residual	800	180	165	37
Crush Resistance	N/cm	lbf/in	N/cm	lbf/in
Short/ long Term	220/110	125/63	100	57
Temperature Ratings	°C	°F	°C	°F
Operation	-40 to +70	-40 to +158	-20 to +70	-4 to +158
Installation*	-30 to +60	-22 to +140	0 to +60	+32 to +140
Storage/Shipping	-40 to +75	-40 to +167	-40 to +70	-40 to +158

* Installation Temperature Range for the 576 to 864 fiber counts is -10C to +60C (-4F to 140F)



Prysmian

4 Tessenere Drive, Highland Heights, KY 41076
na.prysmian.com
TLS-DS-C-101-0624

GenSPEED® COLink Indoor RICT Ribbon

12-864f Riser and 12-144f Plenum RICT Cable



Fiber Count Range	Recommended Fiber Count	Recommended Prysmian** Part Number	Fibers / Ribbon	Number of Ribbons	Buffer Tube OD		Cable OD		Approx. Cable Weight		Max. Reel Length	
					Inches	mm	Inches	mm	lb/kft	kg/km	feet	meters

GenSPEED RICT Indoor Ribbon (Riser)

12 – 48	12	RRICDK-12-AA-012-BB	12	1 – 4	0.24	6.2	0.56	14.3	141	210	39,370	12,000
	24	RRICDK-12-AA-024-BB	12	1 – 4	0.24	6.2	0.56	14.3	141	210	39,370	12,000
	48	RRICDK-12-AA-048-BB	12	1 – 4	0.24	6.2	0.56	14.3	141	210	39,370	12,000
72	72	RRICDK-12-AA-072-BB	12	6 – 12	0.42	10.6	0.60	15.2	111	165	39,370	12,000
84 – 144	144	RRICDK-12-AA-144-BB	12	6 – 12	0.42	10.6	0.60	15.2	111	165	39,370	12,000
240 – 432	432	RRICDK-24-AA-432-BB	24	10 – 18	0.61	15.4	0.90	22.8	245	364	17,864	5,445
576 – 864	576	RRICDK-24-AA-576-BB	24	24	0.81	20.6	1.06	26.8	330	490	12,500	3,800
	864	RRICDK-36-AA-864-BB	36	24	0.81	20.6	1.06	26.8	330	490	12,500	3,800

GenSPEED RICT Indoor Ribbon (Riser with Aluminum Interlock Armor)

12 – 48	12	RRICDKAJ-12-AA-012-BB	12	1 – 4	0.24	6.2	0.91	23.1	401	598	21,394	6,521
	24	RRICDKAJ-12-AA-024-BB	12	1 – 4	0.24	6.2	0.91	23.1	401	598	21,394	6,521
	48	RRICDKAJ-12-AA-048-BB	12	1 – 4	0.24	6.2	0.91	23.1	401	598	21,394	6,521
72	72	RRICDKAJ-12-AA-072-BB	12	6 – 12	0.42	10.6	0.95	24.1	371	552	19,764	6,025
84 – 144	144	RRICDKAJ-12-AA-144-BB	12	6 – 12	0.42	10.6	0.95	24.1	371	552	19,764	6,025
240 – 432	432	RRICDKAJ-24-AA-432-BB	24	10 – 18	0.61	15.4	1.26	32.0	567	844	11,220	3,420
576 – 864	576	RRICDKAJ-24-AA-576-BB	24	24	0.81	20.6	1.4	35.6	723	1,076	9,500	2,900
	864	RRICDKAJ-36-AA-864-BB	36	24	0.81	20.6	1.4	35.6	723	1,076	9,500	2,900

Fiber Count Range	Recommended Fiber Count	Recommended Prysmian** Part Number	Cable Outside Diameter		Tube Outside Diameter		Cable Weight		Maximum Length	
			Inches	mm	Inches	mm	lb/kft	kg/km	feet	meters

GenSPEED RICT Indoor Ribbon (Plenum)

12 – 48	12	RPCDK-12-AA-012-BB	0.45	11.3	0.28	7.1	87	129	15,000	4,000
	24	RPCDK-12-AA-024-BB								
	36	RPCDK-12-AA-036-BB								
	48	RPCDK-12-AA-048-BB								
60 – 144	72	RPCDK-12-AA-072-BB	0.58	14.7	0.39	10.0	156	232	15,000	4,000
	96	RPCDK-12-AA-096-BB								
	120	RPCDK-12-AA-120-BB								
	144	RPCDK-12-AA-144-BB								

* **Note:** This design uses 24 fiber ribbons for counts of 240 to 576 fibers and 36 fiber ribbons for 612 to 864 fibers.
If on reel testing is required for the 612-864 fiber designs, a reel with 60" drum must be specified on the order.

**Where AA equals glass type and BB equals attenuation code



Ordering Guide

The Prysmian Group part number incorporates several significant attributes involving cable design and optical performance. The appropriate part number can be configured using the process described below

GenSPEED® FusionLink™ Indoor Riser Rated Dry Cable:

Example: GenSPEED® FusionLink™ 432 count, riser rated, dry cable with G.652.D LWP single-mode fiber and 0.40/0.40/0.30 attenuation (printed in feet)

1

LENGTH MARKINGS

2

PRODUCT FAMILY

3

FIBER GROUPING

4

FIBER TYPE

5

FIBER COUNT

6

FIBER GRADE

F

–

RRICDK

–

24

–

HB

–

432

–

E1

PART NUMBER CONSTRUCTION	
1	LENGTH MARKINGS
F = Feet or M = Meters	
2	PRODUCT FAMILY & CONSTRUCTION
RRICDK = Dry GenSPEED® Indoor (Riser)	
RRICDKAJ = Dry GenSPEED® Aluminum Interlock Armor Indoor(Riser)	
RPCDK = Dry GenSPEED® Indoor (Plenum)	
3	FIBER GROUPING
12 = 12f Ribbins (12-144)	
24 = 24f Ribbons (240-576)	
36 = 36f Ribbons (864)	

Note: Please refer to the Fiber Code Addendum for additional fiber options, or contact us for help.

FIBER INFORMATION		
4	FIBER TYPE	
SINGLE-MODE		
HB = Single-Mode (ITU G.652 C & D) Low Water Peak – 12-432f only		
B1 = Bend-Insensitive Single-Mode (ITU G.657.A1 & G.652.D)		
B2 = Bend-Insensitive Single-Mode (ITU G.657.A2 & .B2, & G.652.D)		
5	FIBER COUNT	
012 to 864 fibers		
6	FIBER GRADE	
SINGLE-MODE		
Attenuation (dB/km)	Wavelength (nm)	Fiber Type
E1 = 0.40/0.40/0.30	1310/1383/1550	HB, B1, or B2
E3 = 0.35/0.35/0.25	1310/1383/1550	HB, B1, or B2

*576 to 864 fibers limited to E1 attenuation code