


Uniblend® PVC

EPR/Copper Tape Shield/PVC, Medium-Voltage Power, Shielded 25 kV and 35 kV
UL Type MV-105, 133%/100% Ins. Levels, 345 MILS

**Product Construction:****Conductor:**

- 2 AWG thru 1000 kcmil annealed bare copper compact Class B strand

Extruded Strand Shield (ESS):

- Extruded thermoset semi-conducting stress-control layer over conductor

Insulation:

- Lead-free Ethylene Propylene Rubber (EPR) insulation, contrasting in color to the black semi-conducting shield layers

Extruded Insulation Shield (EIS):

- Thermoset semi-conducting polymeric layer free stripping from insulation

Metallic Shield:

- Annealed copper tape with an overlap of 25%

Grounding Conductor:

- 1 bare grounding conductor may be in contact with metallic shielding tape

Overall Jacket:

- Lead-free, moisture- and sunlight-resistant Low-Smoke, Zero-Halogen Polyolefin (LSZH)

Options:

- STRANDFILL® – blocked conductor. Tested in accordance with ICEA T-31-610

Applications:

- Suited for use in a broad range of commercial, industrial and utility applications, where reliability is the major concern, space is limited and ease of installation is critical
- In wet or dry locations when installed in accordance with NEC
- In aerial, direct burial, conduit, open tray and underground duct installations

Features:

- Rated at 105°C
- Excellent heat, moisture and sunlight resistance
- Outstanding corona resistance
- Flexibility for easy handling
- Easy Glider® low friction technology for easy cable pulling
- High dielectric strength
- Low moisture absorption

Features (cont'd):

- Electrical stability under stress
- Low dielectric loss
- Chemical-resistant
- Meets cold bend test at -35°C
- 105°C rating for continuous operation
- 140°C rating for emergency overload conditions
- 250°C rating for short circuit conditions

Compliances:

- National Electrical Code (NEC)
- UL 1072
- ICEA S-93-639/NEMA WC74
- ICEA S-97-682
- ICEA T-33-655
- AIEC CS8 -13 (AIEC CS8-20, Optional)
- CSA C68.10
- CSA C22.2 No. 230 Type TC-ER (Sizes 1/0 AWG and larger)
- UL listed as Type MV-105 for use in accordance with NEC, UL File # E518856
- UL 1685 (70,000 BTU/hr)
- OSHA Acceptable
- RoHS Compliant

Optional Flame Tests:

- IEEE 1202 (70,000 BTU/hr)/CSA FT4

Packaging:

- Material cut to length and shipped on non-returnable wood reels. Lengths in excess of 10,000 lbs. are provided on returnable steel reels that require a deposit
- Extra charges apply for cuts less than 1000 ft., lagging, pulling eyes, paralleling and plexing

CATALOG NUMBER	COND. SIZE (AWG/ kcmil)	NOMINAL CONDUCTOR DIAMETER	INSULATION DIAMETER INCHES		NOMINAL JACKET THICKNESS		NOMINAL CABLE				COPPER WEIGHT		AMPACITY						CONDUIT SIZING (4) (INCHES)
							DIAMETER		WEIGHT				CONDUIT IN AIR (1)		UNDERGROUND DUCT (2)		TRAY (3)		
							IN	mm	LBS/ 1000 FT	kg/ km									
		INCHES	MIN.	MAX.	IN	mm	IN	mm	LBS/ 1000 FT	kg/ km	LBS/ 1000 FT	kg/ km	90°C	105°C	90°C	105°C	90°C	105°C	
25 kV¥ & 35 kV¥¥, UL TYPE MV-105, 133%/100% INS. LEVEL, 345 MILS																			
17061.135105	1/0	0.34	1.020	1.120	0.080	2.03	1.32	33.53	1089	1620	423	629	195	215	200	215	195	220	4
17061.135205	2/0	0.38	1.060	1.160	0.080	2.03	1.36	34.54	1198	1783	511	761	225	255	230	245	225	250	4
17061.135305	3/0	0.42	1.105	1.205	0.080	2.03	1.40	35.56	1351	2011	623	927	260	290	260	275	260	290	4
17061.135405	4/0	0.48	1.160	1.260	0.080	2.03	1.46	37.08	1536	2286	762	1134	295	330	295	315	300	335	4
17061.136005	250	0.52	1.210	1.315	0.080	2.03	1.51	38.35	1695	2522	885	1318	330	365	325	345	335	370	5
17061.136205	350	0.62	1.310	1.410	0.080	2.03	1.61	40.89	2066	3075	1203	1790	395	440	390	415	415	460	5
17061.136505	500	0.74	1.430	1.530	0.080	2.03	1.26	32.00	2608	3882	1674	2491	480	535	465	500	515	575	3.5
17061.137005	750	0.91	1.610	1.710	0.110	2.79	1.98	50.29	3667	5457	2464	3666	585	655	565	610	665	745	6
17061.137505	1000	1.06	1.760	1.865	0.110	2.79	2.15	54.61	4661	6936	3249	4835	675	755	640	690	795	890	6

Dimensions and weights are nominal. Subject to industry tolerances.

* Non-stock item; minimum runs apply. Please consult Customer Service for price and delivery.

(1) Ampacities are in accordance with Table 310.60(C)(73) of the NEC for triplexed or three single conductor copper cables in isolated conduit in air based on a conductor temperature of 90°C (194°F) or 105°C (221°F), temperature denoted in column header, and an ambient air temperature of 40°C (104°F).

(2) Ampacities are in accordance with Table 310.60(C)(77) of the NEC for triplexed or three single conductor copper cables in underground ducts (three conductors per duct), based on a conductor temperature of 90°C (194°F) or 105°C (221°F), temperature denoted in column header, and an ambient earth temperature of 20°C (68°F), electrical duct arrangement per Figure 310.60 Detail 1, 100% load factor, and earth thermal resistance (rho) of 90.

(3) Ampacities are based on single conductor Type MV-105 sizes #1/0 AWG and larger in an uncovered tray in accordance with Section 392.80(B)(2) of the NEC at an ambient air temperature of 40°C (104°F) the ampacities are based on 75% of the values per Table 310.60(C)(69), operating temperature denoted in column header. For cable trays with unventilated covers for more than 6 feet, the ampacities shall not exceed 70% of the values per Table 310.60(C)(69).

(4) Based on nominal cable diameters, three single cables in the duct (PVC Schedule 40) with no ground wire and a maximum of 40% fill. Jam ratio has been considered but should be checked for individual installations.

¥ 100% insulation level is available upon request.

¥¥ 133% insulation level is available upon request.

Note: a) Sizes smaller than 1/0 AWG do not include "FOR CT USE".

b) The NESC Lightning bolt symbol is on all Uniblend® constructions.

