

Uniblend® PVC

EPR/Copper Tape Shield/PVC, Medium-Voltage Power, Shielded 35 kV
UL Type MV-105, 133% Ins. Levels, 420 Mils



Product Construction:

Conductor:

- 1/0 AWG thru 1000 kcmil annealed bare copper compact Class B strand

Extruded Strand Shield (ESS):

- Extruded thermoset semi-conducting stress-control layer over conductor

Insulation:

- Lead-free Ethylene Propylene Rubber (EPR) insulation, contrasting in color to the black semi-conducting shield layers

Extruded Insulation Shield (EIS):

- Thermoset semi-conducting polymeric layer free stripping from insulation

Metallic Shield:

- Annealed copper tape with an overlap of 25%

Jacket:


- Low-friction, lead-free, flame-retardant, moisture- and sunlight-resistant Polyvinyl Chloride (PVC)

Options:

- STRANDFILL® - blocked conductor. Tested in accordance with ICEA T-31-610

Applications:

- Superior performance in petrochemical plants, pulp and paper mills, sewage and water treatment plants, environmental protection systems, railroads, mines, utility power generating stations, steel mills, textile plants and other industrial three-phase applications



Applications (cont'd):

- For use in wet or dry locations when installed in accordance with NEC
- For use in aerial, conduit, open tray and underground duct installations
- For use in direct burial if installed in a system with a ground conductor that is in close proximity, and conforms with NEC 250.4(A)(5)

Features:

- Rated at 105°C
- Easy Glider® low friction technology for easy cable pulling
- Excellent heat, moisture and sunlight resistance
- Excellent flame resistance
- Outstanding corona resistance
- Flexibility for easy handling
- High dielectric strength
- Low moisture absorption
- Electrical stability under stress
- Low dielectric loss
- Chemical-resistant
- Meets cold bend test at -35°C
- 105°C rating for continuous operation
- 140°C rating for emergency overload conditions
- 250°C rating for short circuit conditions

Compliances:

- National Electrical Code (NEC)
- UL 1072
- ICEA S-93-639/NEMA WC74
- ICEA S-97-682
- AEIC CS8 -13 (AEIC CS8-20, Optional)
- CSA C68.10
- CSA C22.2 No. 230 Type TC-ER (Sizes 1/0 AWG and larger)
- UL listed as Type MV-105 for use in accordance with NEC, UL File # E90501
- IEEE 1202 (70,000 BTU/hr)/CSA FT4
- EPA 40 CFR, Part 261 for leachable lead content per TCLP method
- OSHA Acceptable
- RoHS Compliant

Packaging:

- Material cut to length and shipped on non-returnable wood reels. Lengths in excess of 10,000 lbs. are provided on returnable steel reels that require a deposit
- Extra charges apply for cuts less than 1000 ft., lagging, pulling eyes, paralleling and triplexing

CATALOG NUMBER	COND. SIZE (AWG/ kcmil)	NOMINAL CONDUCTOR DIAMETER	INSULATION DIAMETER INCHES		NOMINAL JACKET THICKNESS		NOMINAL CABLE				COPPER WEIGHT		AMPACITY						CONDUIT SIZING (4) (INCHES)
							DIAMETER		WEIGHT				CONDUIT IN AIR (1)		UNDERGROUND DUCT (2)		TRAY (3)		
		INCHES	MIN.	MAX.	IN	mm	IN	mm	LBS/ 1000 FT	kg/ km	LBS/ 1000 FT	kg/ km	90°C	105°C	90°C	105°C	90°C	105°C	
35 kV, UL TYPE MV-105, 133% INS. LEVEL, 420 MILS																			
17071.135105	1/0	0.34	1.060	1.265	0.080	2.03	1.49	37.77	1292	1922	436	648	195	215	200	215	195	220	5
17071.135205	2/0	0.38	1.200	1.305	0.080	2.03	1.53	38.79	1412	2102	524	780	225	255	230	245	225	250	5
17071.135305	3/0	0.42	1.245	1.355	0.080	2.03	1.57	39.98	1566	2330	636	946	260	290	260	275	260	290	5
17071.135405	4/0	0.48	1.300	1.405	0.080	2.03	1.63	41.28	1757	2615	775	1153	295	330	295	315	300	335	5
17071.136005	250	0.52	1.350	1.460	0.080	2.03	1.68	42.77	1924	2863	898	1337	330	365	325	345	335	370	5
17071.136205	350	0.62	1.450	1.555	0.110	2.79	1.86	47.27	2465	3668	1216	1809	395	440	390	415	415	460	6
17071.136505	500	0.74	1.570	1.675	0.110	2.79	1.98	50.22	3032	4512	1687	2511	480	535	465	500	515	575	6
17071.137005	750	0.91	1.750	1.860	0.110	2.79	2.15	54.53	3960	5893	2477	3685	585	655	565	610	665	745	6
17071.137505	1000	1.06	1.900	2.010	0.110	2.79	2.32	58.93	4976	7406	3262	4854	675	755	640	690	795	890	8

Dimensions and weights are nominal. Subject to industry tolerances.

* Non-stock item; minimum runs apply. Please consult Customer Service for price and delivery.

(1) Ampacities are in accordance with Table 310.60(C)(73) of the NEC for triplexed or three single conductor copper cables in isolated conduit in air based on a conductor temperature of 90°C (194°F) or 105°C (221°F), temperature denoted in column header, and an ambient air temperature of 40°C (104°F).

(2) Ampacities are in accordance with Table 310.60(C)(77) of the NEC for triplexed or three single conductor copper cables in underground ducts (three conductors per duct), based on a conductor temperature of 90°C (194°F) or 105°C (221°F), temperature denoted in column header, and an ambient earth temperature of 20°C (68°F), electrical duct arrangement per Figure 310.60 Detail 1, 100% load factor, and earth thermal resistance (rho) of 90.

(3) Ampacities are based on single conductor Type MV-105 sizes #1/0 AWG and larger in an uncovered tray in accordance with Section 392.80(B)(2) of the NEC at an ambient air temperature of 40°C (104°F) the ampacities are based on 75% of the values per Table 310.60(C)(69), operating temperature denoted in column header. For cable trays with unventilated covers for more than 6 feet, the ampacities shall not exceed 70% of the values per Table 310.60(C)(69).

(4) Based on nominal cable diameters, three single cables in the duct (PVC Schedule 40) with no ground wire and a maximum of 40% fill. Jam ratio has been considered but should be checked for individual installations.

Note: a) All sizes are "FOR CT USE".

b) The NESC Lightning bolt symbol is on all Uniblend® constructions.